



DUST REMOVAL SYSTEM SUBMITTALS

Drilling

- Self-contained drilling systems (TE 4A/6A DRS) (TE 7/7C DRS-M)
- Rotary hammers with DRS-S
- DRS-C
- Combihammers with DRS-Y
- DRS-D
- Hollow drill bits
- Core drilling with WMS 100

Chiseling

- Breakers with DRS-B and DRS-3000

Cutting and grinding

- Cutting/tuck-pointing with grinders
- Gas saws with DSH-P (section ii)
- Grinding concrete with grinders

Vacuums

- VC 75-1-A22
- VC 125-9
- VC 150-6 X
- VC 150-10 X
- VC 150-6 XE
- VC 150-10 XE
- VC 300-17 X





HILTI SUBMITTAL PACKAGE OSHA 1926.1153 TABLE 1, SECTION vii:

**Handheld and stand-mounted drills
(including impact and
rotary hammer drills)**

**Current Hilti self-contained dust collection systems:
DRS 4-A
DRS 6-A
DRS-M**



 For instructions on how to assemble these systems, please refer to the Hilti North America Youtube page

 Onboard systems

OSHA 1926.1153 TABLE 1 REQUIREMENTS

These systems fall under OSHA 1926.1153 table 1, **section vii: handheld and stand-mounted drills (including impact and rotary hammer drills)**. In order to be OSHA 1926.1153 table 1 compliant, the below requirements must be met:

- Use drill equipped with commercially available shroud or cowling with dust collection system
- Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions
- Dust collector must provide the air flow recommended by the tool manufacturer, or greater
- Have a filter with 99% or greater efficiency and a filter-cleaning mechanism

Note: Vacuum must be equipped with a HEPA-filter when cleaning holes

OSHA 1926.1153 Table 1 states that no respirator is required if the above controls are fully and properly implemented.

Equipment / Task	Engineering and work practice control methods	Required respiratory protections and minimum Assigned Protection Factor (APF)	
		≤ 4 hours / shift	> 4 hours / shift
Handheld and stand-mounted drills (including impact and rotary hammer drills)	Use drill equipped with commercially available shroud or cowling with dust collection system. Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions. Dust collector must provide the air flow recommended by the tool manufacturer, or greater, and have a filter with 99% or greater efficiency and a filter-cleaning mechanism. Use a HEPA-filtered vacuum when cleaning holes.	None	None
		None	None

Check below to see how your system can be compliant with OSHA 1926.1153. To verify the generation of your tool, check the rating plate, or call Hilti at 800-879-8000 with your serial number.

DRS module name	Tool name and generation	DRS system item number	Method of compliance
DRS 4-A	TE 4-A gen 1	n/a	Exposure assessment
	TE 4-A gen 2	2098490**	Objective data*
DRS 6-A	TE 6-A gen 1	2177080	Objective data* / OSHA 1926.1153 Table 1
	TE 6-A gen 2	n/a	Exposure assessment
	TE 6-A gen 3	n/a	Exposure assessment
	TE 6-A gen 4	2040914	Objective data
	TE 6-A gen 4	2172902	Objective data* / OSHA 1926.1153 Table 1
DRS-M	TE 6 / 6-S / 7 / 7-C / TE 7-A	2098511**	Objective data*
		267769	Objective data*

*See Hilti’s published Objective Data — if not applicable to a specific application, exposure assessment is required.

**Can be upgraded to OSHA 1926.1153 table 1 compliance through purchase of the compliant filter box

SYSTEM OVERVIEW

Self-contained dust-collection systems are systems that fit on the tool and do not require a separate stand-alone vacuum to collect dust. Hilti currently offers the below systems with this configuration:

Tool	Accessory	Vacuum
 <p data-bbox="152 800 488 821">Rotary hammer TE 4-A 18 or TE 4-A 22</p>	 <p data-bbox="664 800 954 821">Dust removal system TE DRS 4-A</p>	
 <p data-bbox="207 1163 435 1184">Rotary hammer TE 6-A 36</p>	 <p data-bbox="664 1163 954 1184">Dust removal system TE DRS 6-A</p>	
 <p data-bbox="188 1543 451 1564">Rotary hammer TE 7 or TE 7-C</p>	 <p data-bbox="670 1543 948 1564">Dust removal system TE DRS-M</p>	

Note: previous generations of tools may have different item numbers or nomenclature. Check with your local Hilti representative or product instruction manual to verify

OSHA 29 CFR §1926.1153 RESPIRABLE SILICA DUST EXPOSURE

Hilti TE 4-A/6-A with on-board dust removal system (DRS)

Hilti has performed testing of the above system to determine the operator's respirable silica dust exposure in accordance with EN 50632-1 and EN 50632-2-6¹. Testing was performed under the following conditions:

- Room size: 7.8m x 7.8m x 3.3m Closed — no air exchange
- Drilled hole dimensions: $\varnothing 5/8'' \times 2''$
- Test duration: 1 hour
- Total holes drilled: 75
- Drilling orientation: overhead
- Base material: concrete
- Sampler: 10 l/min GSP pump, FSP sampler, ISO 7708-compliant, 5 μm filter
- Air sample volume collected during test: 600 liters
- Dust collection receptacle on tool emptied every 8 holes drilled



DRS module items 2098490 (TE 4A gen 2) and 2172902 (TE 6A gen 4) only

Results:

Time-Weighted Average Respirable Silica Dust Exposure^{2,3}	45 $\mu\text{g}/\text{m}^3$
--	---

- 1 Exception: EN 50632-2-6 specifies drilling one hundred twenty $\varnothing 16\text{mm} \times 50\text{mm}$ holes at a 15° downward-from-horizontal position.
- 2 The silica content of base materials varies. As a result, the silica content in respirable dust samples also varies. The above-published exposure value is based on a 20% silica content applied to the total respirable dust measurement. Measured average silica content during testing was 13.8%.
- 3 Exposure value represents the time-weighted average (TWA) over the 1-hour test period. Due to the test being conducted in a closed, non-ventilated room, this TWA exposure value would increase if the test duration was extended under the same conditions.
- 4 These test results can be applied for modules used with previous generations of tools.

HOW TO USE THE OSHA 1926.1153 TABLE 1 SOLUTION

Cordless rotary hammer

TE DRS OSHA

Hilti developed TE DRS dust collection system with a filter cleaning mechanism and 99% filter efficiency, compliant with OSHA 1926.1153 Table 1. The TE DRS-4-A dust box is compatible with the TE DRS-4-A and TE DRS-4-A (T1) only. The TE DRS-6-A dust box is compatible with the TE DRS-6-A and TE DRS-6-A (T1) only.

Set-up

1. Empty the TE DRS dust box, and clean and inspect the filter.
2. Attach the TE DRS module to the rotary hammer.
3. Start TE DRS vacuum by pressing tool's control switch.
4. Verify proper operation of the TE DRS vacuum, including suction at the extraction head.
 - Check for damage or leaks in the dust box, hose, and extraction head.
 - Make sure the hose extends/retracts freely.

Drilling

1. Start drilling, and allow the TE DRS to reach full speed before beginning to drill.
 - Hold the rotary hammer perpendicular to the work surface and keep the extraction head in contact with the work surface.
2. To maximize dust collection, after the hole is drilled, slowly withdraw bit from the hole, and keep the rotary hammer running until the bit is fully withdrawn.

Cleaning and maintenance

- Empty the dust box after every 5 in³ of hole drilling (e.g. after 8-10 holes 5/8 in x 2 in (16 mm x 50 mm)).
- After every 3 in³ of hole drilling (e.g. after 5 holes \varnothing 1/2 in depth 3 in (\varnothing 12 mm x 76 mm)) or if suction performance decreases push the button of the cleaning mechanism 5 times in each direction.
- To minimize dust emission, either use a vacuum to clean the dust box or place the dust box in a plastic bag keeping it closed as much as possible.
- Replace the filter if the dust debris cannot be removed, or if there are any tears or leaks in the filter.
- If more-than-usual dust is emitted during drilling, inspect the TE DRS system, and clean/inspect the dust box and filter.



HILTI SUBMITTAL PACKAGE OSHA 1926.1153 TABLE 1, SECTION vii

Section vii: Handheld and stand-mounted drills (including impact and rotary hammer drills)

Current Hilti rotary hammers that use a DRS-S shroud:

- TE 2 (and 2-S)
- TE 3-C
- TE 4-A 22
- TE 6-A 36
- TE 7
- TE 7-C
- TE 30 (and 30-C)
- TE 40-AVR
- TE 50-AVR
- TE 60 A-36
- TE 60-AVR
- TE 60-ATC/AVR
- TE 70-AVR
- TE 70-ATC/AVR
- TE 80-ATC/AVR

 For instructions on how to assemble these systems, please refer to the Hilti North America Youtube page

 DRS-S

OSHA 1926.1153 TABLE 1 REQUIREMENTS

These systems fall under OSHA 1926.1153 table 1, **section vii: handheld and stand-mounted drills (including impact and rotary hammer drills)**. In order to be OSHA 1926.1153 table 1 compliant, the below requirements must be met:

- Use drill equipped with commercially available shroud or cowling with dust collection system
- Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions
- Dust collector must provide the air flow recommended by the tool manufacturer, or greater
- Have a filter with 99% or greater efficiency and a filter-cleaning mechanism

Note: Vacuum must be equipped with a HEPA-filter when cleaning holes

OSHA 1926.1153 Table 1 states that no respirator is required if the above controls are fully and properly implemented.

Equipment / Task	Engineering and work practice control methods	Required respiratory protections and minimum Assigned Protection Factor (APF)	
		≤ 4 hours / shift	> 4 hours / shift
Handheld and stand-mounted drills (including impact and rotary hammer drills)	Use drill equipped with commercially available shroud or cowling with dust collection system. Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions. Dust collector must provide the air flow recommended by the tool manufacturer, or greater, and have a filter with 99% or greater efficiency and a filter-cleaning mechanism. Use a HEPA-filtered vacuum when cleaning holes.	None	None
		None	None

Check below to see how your system can be compliant with OSHA 1926.1153 Table 1. To verify the generation of your tool, check the rating plate, or call Hilti at 800-879-8000 with your serial number.

DRS module name	Tool name and generation	Vacuums (can use any)	Method of compliance
TE 2 series TE 3-C series TE 7 series TE 4-A 22 TE 6-A 36 TE 30 series TE 30-A 36 TE 40-AVR	DRS-S (Item number 340602)	VC 75-1-A22 ¹ VC 125-9 VC 20-U VC 40-U VC 40-UE VC 150-6 X VC 150-10 X VC 150-6 XE VC 150-10 XE	All OSHA 1926.1153 table 1 compliant
TE 50-AVR TE 60 series TE 70 series TE 80-ATC/AVR	Depth gauge* and DRS-S required	VC 300-17 X	

*The correct depth gauge will depend on your model of tool. For questions, check your instruction manual or call Hilti at 800-879-8000.

¹ If a decrease in suction occurs with the VC 75-1-A22, Hilti’s manufacturer guidelines recommends pushing the filter cleaning button on the tool to clear the filter.

SYSTEM OVERVIEW

Hilti rotary hammers with a DRS-S are OSHA 1926.1153 table 1 compliant through use of a dust collection shroud hooked up to a vacuum that meets OSHA 1926.1153 table 1 requirements. This shroud attaches to the depth gauge on the tool, and must be purchased separately for tools with an SDS-max connection. Any Hilti rotary hammer with a depth gauge will be OSHA 1926.1153 table 1 compliant with the DRS-S if a Hilti vacuum is used. Hilti currently offers the below systems with this configuration:

Tool	Accessory	Vacuum (use any)
 <p>TE 2 and TE 2-S</p>	 <p>DRS-S</p>	 <p>VC 75-1-A22¹</p>
 <p>TE 3-C</p>		 <p>VC 125-6</p>  <p>VC 125-9</p>
 <p>TE 7 and TE 7-C</p>  <p>TE 4-A 22</p>		 <p>VC 20-U</p>  <p>VC 150-6 X</p>
 <p>TE 6-A 36</p>  <p>TE 7-A</p>		 <p>VC 150-6 XE</p>  <p>VC 40-U</p>
 <p>TE 30 and TE 30-C</p>  <p>TE 30-A 36</p>		 <p>VC 150-10 X</p>  <p>VC 40-UE</p>
 <p>TE 40-AVR</p>		 <p>VC 150-10 XE</p>  <p>VC 300-17 X</p>

Note: previous generations of tools may have different item numbers or nomenclature. Check with your local Hilti representative or product instruction manual to verify

1 If a decrease in suction occurs with the VC 75-1-A22, Hilti's manufacturer guidelines recommends pushing the filter cleaning button on the tool to clear the filter.

Tool	Accessory	Vacuum (use any)	
 TE 50-AVR		 VC 75-1-A22 ¹	
 TE 60-A36		 VC 125-6	 VC 125-9
 TE 60-AVR		 VC 20-U	 VC 150-6 X
 TE 60-ATC/AVR	 Depth gauge (sold separately)	 VC 150-6 XE	 VC 40-U
 TE 70-AVR	 DRS-S	 VC 150-10 X	 VC 40-UE
 TE 70-ATC/AVR		 VC 150-10 XE	 VC 300-17 X
 TE 80-ATC/AVR			

Note: previous generations of tools may have different item numbers or nomenclature. Check with your local Hilti representative or product instruction manual to verify
 1 If a decrease in suction occurs with the VC 75-1-A22, Hilti's manufacturer guidelines recommends pushing the filter cleaning button on the tool to clear the filter.

DRILLING — ROTARY HAMMER DRILLS AND COMBI-HAMMERS

TE Dust Control — OSHA

Hilti developed drilling dust collection systems with a shroud, to be attached to a Hilti vacuum with a filter cleaning mechanism and 99% filter efficiency, compliant with OSHA 1926.1153, Table 1.

Set-up

1. Attach the appropriate dust collection shroud to the drill.
2. Insert the bit. Rotate the bit in the chuck until you hear a clicking noise to verify that the bit is firmly inserted into the chuck.
3. Choose the correct collector based on the system and insert being used.
4. Set the proper depth using the depth gauge mechanism on the shroud. This will either be a depth gauge rod (DRS-Y, hollow drill bits) or a set of tabbed stops (DRS 4-A/6-A/M, DRS-S)
5. Verify that the bit is flush or below the surface of the dust collection device. Note that for the DRS-Y, with 24" bits, the bit will extend approximately 1" beyond the shroud.
6. Make sure that drilling shroud extends and retracts freely.
7. Start vacuum.
8. Verify proper operation of the dust collection system, including suction at the extraction head.
 - Check for damage or leaks in the vacuum, hose, and extraction head.
 - See instructions for vacuum.

Drilling

1. Start the vacuum before beginning to drill.
 - Hold the drill perpendicular to the work surface and keep the extraction head in contact with the work surface.
2. To maximize dust collection, after the hole is drilled, slowly withdraw bit from the hole, and keep the drill running until the bit is fully withdrawn.

Cleaning and maintenance

- See instructions for vacuum.



HILTI SUBMITTAL PACKAGE OSHA 1926.1153 TABLE 1, SECTION vii

**Section vii: Handheld and
stand-mounted drills
(including impact and
rotary hammer drills)**

Current Hilti rotary hammers that use a DRS-C shroud:

- TE 3-C/-M
- TE 7/-C
- TE 4-A 22
- TE 6-A 22/36
- TE 30 (30-C and A36)
- TE 300-A



OSHA 1926.1153 TABLE 1 REQUIREMENTS

These systems fall under OSHA 1926.1153 Table 1, **section vii: handheld and stand-mounted drills (including impact and rotary hammer drills)**. In order to be OSHA 1926.1153 Table 1 compliant, the below requirements must be met:

- Use drill equipped with commercially available shroud or cowling with dust collection system
- Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions
- Dust collector must provide the air flow recommended by the tool manufacturer, or greater
- Have a filter with 99% or greater efficiency and a filter-cleaning mechanism

Note: Vacuum must be equipped with a HEPA-filter when cleaning holes

OSHA 1926.1153 Table 1 states that no respirator is required if the above controls are fully and properly implemented.

Equipment / Task	Engineering and work practice control methods	Required respiratory protections and minimum Assigned Protection Factor (APF)	
		≤ 4 hours / shift	> 4 hours / shift
Handheld and stand-mounted drills (including impact and rotary hammer drills)	Use drill equipped with commercially available shroud or cowling with dust collection system. Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions. Dust collector must provide the air flow recommended by the tool manufacturer, or greater, and have a filter with 99% or greater efficiency and a filter-cleaning mechanism. Use a HEPA-filtered vacuum when cleaning holes. • When used outdoors	None	None
		None	None

Check below to see how your system can be compliant with OSHA 1926.1153 Table 1. To verify the generation of your tool, check the rating plate, or call Hilti at 800-879-8000 with your serial number.

DRS module name	Tool name and generation	Vacuums (can use any)	Method of compliance
TE 3-C/-M TE 7/-C TE 4-A 22 TE 6-A 22/36 TE 30 (30-C and A36) TE 300-A	DRS-C (Item number 2213351)	VC 75-1-A22 ¹ VC 125-6 VC 125-9 VC 20-U VC 40-U VC 40-UE VC 150-6 XE VC 150-10 XE VC 300-17 X	All OSHA 1926.1153 Table 1 compliant

¹ If a decrease in suction occurs with the VC 75-1-A22, Hilti’s manufacturer guidelines recommends pushing the filter cleaning button on the tool to clear the filter.

SYSTEM OVERVIEW

Hilti rotary hammers with a DRS-D are OSHA 1926.1153 Table 1 compliant through use of a dust collection shroud hooked up to a vacuum that meets OSHA 1926.1153 Table 1 requirements. This shroud attaches to the vacuum and suctions itself to the drilling surface, the drill is then placed in the center of the DRS-D opening to start drilling.

Hilti currently offers the below systems with this configuration:

Tool	Accessory	Vacuum (use any)	
 <p>TE 3-C</p>	 <p>DRS-C</p>	 <p>VC 75-1-A22¹</p>	
 <p>TE 7 and TE 7-C</p>  <p>TE 4-A 22</p>		 <p>VC 125-6</p>  <p>VC 125-9</p>	
 <p>TE 6-A 36</p>  <p>TE 7-A</p>		 <p>VC 20-U</p>  <p>VC 40-U</p>	
 <p>TE 30 and TE 30-C</p>  <p>TE 30-A 36</p>		 <p>VC 150-6 XE</p>  <p>VC 40-UE</p>	
			 <p>VC 150-10 XE</p>  <p>VC 300-17 X</p>

Note: previous generations of tools may have different item numbers or nomenclature. Check with your local Hilti representative or product instruction manual to verify

¹ If a decrease in suction occurs with the VC 75-1-A22, Hilti's manufacturer guidelines recommends pushing the filter cleaning button on the tool to clear the filter.

DRILLING — ROTARY HAMMER DRILLS AND COMBI-HAMMERS

TE Dust Control — OSHA

Hilti developed drilling dust collection systems with a shroud, to be attached to a Hilti vacuum with a filter cleaning mechanism and 99% filter efficiency, compliant with OSHA 1926.1153, Table 1.

Set-up

1. Attach the appropriate dust collection shroud to the drill.
2. Insert the bit. Rotate the bit in the chuck until you hear a clicking noise to verify that the bit is firmly inserted into the chuck.
3. Choose the correct collector based on the system and insert being used.
4. Set the proper depth using the depth gauge mechanism on the shroud. This will either be a depth gauge rod (DRS-C, hollow drill bits) or a set of tabbed stops (DRS 4-A/6-A/M, DRS-S). A depth gauge is not needed on the DRS-C when using the attachments for chiseling.
5. Verify that the bit is flush or below the surface of the dust collection device. Note that for the DRS-C, with 24" bits, the bit will extend approximately 1" beyond the shroud. When chiseling with the DRS-C, the chisel will extend beyond the head of the chiseling shroud to allow the insert to chisel.
6. When drilling, make sure that drilling shroud extends and retracts freely.
7. Start vacuum.
8. Verify proper operation of the dust collection system, including suction at the extraction head
 - Check for damage or leaks in the vacuum, hose, and extraction head.
 - See instructions for vacuum.

Drilling

1. Start to drill.
 - Hold the drill perpendicular to the work surface and keep the bit in contact with the work surface inside the DRS-D.
2. To maximize dust collection, after the hole is drilled, slowly withdraw bit from the hole, and keep the drill running until the bit is fully withdrawn.

Cleaning and maintenance

- See instructions for vacuum.



HILTI SUBMITTAL PACKAGE OSHA 1926.1153 TABLE 1, SECTION x AND SECTION vii

**Section x: Jackhammers and handheld
powered chipping tools**

**Section vii: Handheld and stand-mounted drills
(including impact and
rotary hammer drills)**

Current Hilti SDS-max rotary hammers that use a DRS-Y shroud:

- TE 50-AVR
- TE 60-A36
- TE 60-AVR
- TE 60-ATC/AVR
- TE 70-AVR
- TE 70-ATC/AVR
- TE 80-ATC/AVR



 For instructions on how to assemble these systems, please refer to the Hilti North America Youtube page

 DRS-Y

OSHA 1926.1153 TABLE 1 REQUIREMENTS

These systems fall under OSHA 1926.1153 table 1, **section x: jackhammers and handheld powered chipping tools and section vii: handheld and stand-mounted drills (including impact and rotary hammer drills)**. In order to be OSHA 1926.1153 table 1 compliant, the below requirements must be met:

Options for chiseling applications

- Use tool with water delivery system that supplies a continuous stream or spray of water at the point of impact

OR

Options for drilling or chiseling applications

- Use tool equipped with commercially available shroud or cowling with dust collection system
- Operate and maintain tool in accordance with manufacturer's instructions to minimize dust emissions
- Dust collector must provide the air flow recommended by the tool manufacturer, or greater
- Have a filter with 99% or greater efficiency and a filter-cleaning mechanism

Note: Vacuum must be equipped with a HEPA-filter when cleaning holes

OSHA 1926.1153 Table 1 requires a respirator to be worn in certain environments based on the time of the application. Check below to see when an APF 10 respirator must be worn.

Equipment / Task	Engineering and work practice control methods	Required respiratory protections and minimum Assigned Protection Factor (APF)	
		≤ 4 hours / shift	> 4 hours / shift
Handheld and stand-mounted drills (including impact and rotary hammer drills)	Use drill equipped with commercially available shroud or cowling with dust collection system. Operate and maintain tool in accordance with manufacturer's instructions to minimize dust emissions. Dust collector must provide the air flow recommended by the tool manufacturer, or greater, and have a filter with 99% or greater efficiency and a filter-cleaning mechanism. Use a HEPA-filtered vacuum when cleaning holes.	None	None
	<ul style="list-style-type: none"> • When used outdoors 	None	None
Jackhammers and handheld powered chipping tools	Use tool with water delivery system that supplies a continuous stream or spray of water at the point of impact.	None	APF 10
	<ul style="list-style-type: none"> • When used outdoors • When used indoors or in an enclosed area 	APF 10	APF 10
OR			
	Use tool equipped with commercially available shroud and dust collection system. Operate and maintain tool in accordance with manufacturer's instructions to minimize dust emissions. Dust collector must provide the air flow recommended by the tool manufacturer, or greater, and have a filter with 99% or greater efficiency and a filter-cleaning mechanism.	None	APF 10
	<ul style="list-style-type: none"> • When used outdoors • When used indoors or in an enclosed area 	APF 10	APF 10

Check below to see how your system can be compliant with OSHA 1926.1153 Table 1. To verify the generation of your tool, check the rating plate, or call Hilti at 800-879-8000 with your serial number. To check fit of the DRS-Y with older tool generations, check the sticker on the inside of the case on the DRS-Y, or refer to the instruction manual.

Tool models*	Accessory	Vacuums (can use any)	Method of compliance
TE 50 TE 50-AVR TE 60-A36 TE 60 TE 60-AVR TE 60-ATC/AVR TE 70-AVR TE 70-ATC/AVR TE 80-ATC/AVR	DRS-Y (Item number 2055718)	VC 75-1-A22 ¹ VC 125-6 VC 125-9 VC 20-U VC 40-U VC 40-UE VC 150-6 X VC 150-10 X VC 150-6 XE VC 150-10 XE VC 300-17 X	All OSHA 1926.1153 table 1 compliant

SYSTEM OVERVIEW

Hilti SDS-max rotary hammers are OSHA 1926.1153 table 1 compliant for both drilling and chiseling applications through use of a dust collection shroud hooked up to a vacuum that meets OSHA 1926.1153 table 1 requirements. Hilti currently offers the below systems with this configuration:

Tool	Accessory	Vacuum (use any)
		
TE 50-AVR		VC 75-1-A22 ¹
		
TE 60-A36		VC 125-6
		
TE 60-AVR		VC 125-9
		
TE 60-ATC/AVR	TE DRS-Y	VC 20-U
		
TE 70-AVR		VC 150-6 X
		
TE 70-ATC/AVR		VC 40-U
		
TE 80-ATC/AVR		VC 150-10 X
		
		VC 40-UE
		
		VC 150-10 XE
		
		VC 300-17 X

Note: previous generations of tools may have different item numbers or nomenclature. Check with your local Hilti representative or product instruction manual to verify
 1 If a decrease in suction occurs with the VC 75-1-A22, Hilti's manufacturer guidelines recommends pushing the filter cleaning button on the tool to clear the filter.

DRILLING — ROTARY HAMMER DRILLS AND COMBI-HAMMERS

TE Dust Control — OSHA

Hilti developed drilling dust collection systems with a shroud, to be attached to a Hilti vacuum with a filter cleaning mechanism and 99% filter efficiency, compliant with OSHA 1926.1153, Table 1.

Set-up

1. Attach the appropriate dust collection shroud to the drill.
2. Insert the bit. Rotate the bit in the chuck until you hear a clicking noise to verify that the bit is firmly inserted into the chuck.
3. Choose the correct collector based on the system and insert being used.
4. Set the proper depth using the depth gauge mechanism on the shroud. This will either be a depth gauge rod (DRS-Y, hollow drill bits) or a set of tabbed stops (DRS 4-A/6-A/M, DRS-S). A depth gauge is not needed on the DRS-Y when using the attachments for chiseling.
5. Verify that the bit is flush or below the surface of the dust collection device. Note that for the DRS-Y, with 24" bits, the bit will extend approximately 1" beyond the shroud. When chiseling with the DRS-Y, the chisel will extend beyond the head of the chiseling shroud to allow the insert to chisel.
6. When drilling, make sure that drilling shroud extends and retracts freely.
7. Start vacuum.
8. Verify proper operation of the dust collection system, including suction at the extraction head
 - Check for damage or leaks in the vacuum, hose, and extraction head.
 - See instructions for vacuum.

Drilling

1. Start the vacuum before beginning to drill.
 - Hold the drill perpendicular to the work surface and keep the extraction head in contact with the work surface.
2. To maximize dust collection, after the hole is drilled, slowly withdraw bit from the hole, and keep the drill running until the bit is fully withdrawn.

Cleaning and maintenance

- See instructions for vacuum.



HILTI SUBMITTAL PACKAGE OSHA 1926.1153 TABLE 1, SECTION vii

**Section vii: Handheld and
stand-mounted drills
(including impact and
rotary hammer drills)**

Current Hilti rotary hammers that use a DRS-D shroud:

- TE 2 (and 2-S)
- TE 3-C
- TE 7
- TE 4-A 22
- TE 6-A 36
- TE 7-C
- TE 30 (and 30-C)
- TE 30-A36
- TE 40-AVR
- TE 50-AVR
- TE 60-A36
- TE 60-AVR
- TE 60-ATC/AVR
- TE 70-AVR
- TE 70-ATC/AVR
- TE 80-ATC/AVR



For instructions on how to assemble these systems, please refer to the Hilti North America Youtube page

OSHA 1926.1153 TABLE 1 REQUIREMENTS

These systems fall under OSHA 1926.1153 Table 1, **section vii: handheld and stand-mounted drills (including impact and rotary hammer drills)**. In order to be OSHA 1926.1153 Table 1 compliant, the below requirements must be met:

- Use drill equipped with commercially available shroud or cowling with dust collection system
- Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions
- Dust collector must provide the air flow recommended by the tool manufacturer, or greater
- Have a filter with 99% or greater efficiency and a filter-cleaning mechanism

Note: Vacuum must be equipped with a HEPA-filter when cleaning holes

Table 1 states that no respirator is required if the above controls are fully and properly implemented.

Equipment / Task	Engineering and work practice control methods	Required respiratory protections and minimum Assigned Protection Factor (APF)	
		≤ 4 hours / shift	> 4 hours / shift
Handheld and stand-mounted drills (including impact and rotary hammer drills)	Use drill equipped with commercially available shroud or cowling with dust collection system. Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions. Dust collector must provide the air flow recommended by the tool manufacturer, or greater, and have a filter with 99% or greater efficiency and a filter-cleaning mechanism. Use a HEPA-filtered vacuum when cleaning holes.	None	None
		None	None

Check below to see how your system can be compliant with OSHA 1926.1153 Table 1. To verify the generation of your tool, check the rating plate, or call Hilti at 800-879-8000 with your serial number.

DRS module name	Tool name and generation	Vacuums (can use any)	Method of compliance
TE 2 series TE 3-C series TE 7 series TE 4-A 22 TE 6-A 36 TE 30 series TE 30-A 36 TE 40-AVR TE 50-AVR TE 60 series TE 60-A36 TE 70 series TE 80-ATC/AVR	DRS-D (Item number 2191207)	VC 75-1-A22 ^{1,2} VC 125-6 VC 125-9 VC 20-U VC 40-U VC 40-UE VC 150-6 XE VC 150-10 XE VC 300-17 X	All OSHA 1926.1153 Table 1 compliant

1 If a decrease in suction occurs with the VC 75-1-A22, Hilti’s manufacturer guidelines recommends pushing the filter cleaning button on the tool to clear the filter.
 2 When used with the DRS-D with an SDS-Max tool, the VC 75 can be used for dust collection when drilling diameters up to 32 mm when used on wall and floor applications.

SYSTEM OVERVIEW

Hilti rotary hammers with a DRS-D are OSHA 1926.1153 Table 1 compliant through use of a dust collection shroud hooked up to a vacuum that meets OSHA 1926.1153 Table 1 requirements. This shroud attaches to the vacuum and suctions itself to the drilling surface, the drill is then placed in the center of the DRS-D opening to start drilling.

Hilti currently offers the below systems with this configuration:

Tool	Accessory	Vacuum (use any)
 <p>TE 2-A 18</p>		 <p>VC 75-1-A22¹</p>
 <p>TE 2 and TE 2-S</p>		 <p>VC 125-6</p>  <p>VC 125-9</p>
 <p>TE 3-C</p>		 <p>VC 20-U</p>  <p>VC 40-U</p>
 <p>TE 7 and TE 7-C</p>  <p>TE 4-A 22</p>	 <p>DRS-D</p>	 <p>VC 150-6 XE</p>  <p>VC 40-UE</p>
 <p>TE 6-A 36</p>  <p>TE 7-A</p>		 <p>VC 150-10 XE</p>  <p>VC 300-17 X</p>
 <p>TE 30 and TE 30-C</p>  <p>TE 30-A 36</p>		
 <p>TE 40-AVR</p>		

Note: previous generations of tools may have different item numbers or nomenclature. Check with your local Hilti representative or product instruction manual to verify
 1 If a decrease in suction occurs with the VC 75-1-A22, Hilti's manufacturer guidelines recommends pushing the filter cleaning button on the tool to clear the filter.

Tool	Accessory	Vacuum (use any)	
 TE 50-AVR			
 TE 60-A36		 VC 75-1-A22 ^{1,2}	
 TE 60-AVR		 VC 125-6	 VC 125-9
 TE 60-ATC/AVR		 VC 20-U	 VC 40-U
 TE 60-A36	 DRS-D	 VC 150-6 XE	 VC 40-UE
 TE 70-AVR		 VC 150-10 XE	 VC 300-17 X
 TE 70-ATC/AVR			
 TE 80-ATC/AVR			

Note: previous generations of tools may have different item numbers or nomenclature. Check with your local Hilti representative or product instruction manual to verify

1 If a decrease in suction occurs with the VC 75-1-A22, Hilti's manufacturer guidelines recommends pushing the filter cleaning button on the tool to clear the filter.

2 When used with the DRS-D with an SDS-Max tool, the VC 75 can be used for dust collection when drilling diameters up to 32 mm when used on wall and floor applications.

DRILLING — ROTARY HAMMER DRILLS AND COMBI-HAMMERS

TE Dust Control — OSHA

Hilti developed drilling dust collection systems with a shroud, to be attached to a Hilti vacuum with a filter cleaning mechanism and 99% filter efficiency, compliant with OSHA 1926.1153, Table 1.

Set-up

1. Attach the DRS-D to the vacuum.
2. Insert the bit. Rotate the bit in the chuck until you hear a clicking noise to verify that the bit is firmly inserted into the chuck.
3. Turn on the vacuum, making sure automatic filter cleaning is turned off.
4. Place DRS-D onto drilling surface.
5. Verify that the DRS-D is flush to the wall and has sealed itself in place.
6. Verify proper operation of the dust collection system.
 - Check for damage or leaks in the vacuum, hose, and extraction head.
 - See instructions for vacuum.
 - See instructions for vacuum.

Drilling

1. Start to drill.
 - Hold the drill perpendicular to the work surface and keep the bit in contact with the work surface inside the DRS-D.
2. To maximize dust collection, after the hole is drilled, slowly withdraw bit from the hole, and keep the drill running until the bit is fully withdrawn.

Cleaning and maintenance

- See instructions for vacuum.



HILTI SUBMITTAL PACKAGE OSHA 1926.1153 TABLE 1, SECTION vii

**Section vii: Handheld and
stand-mounted drills
(including impact and
rotary hammer drills)**

All Hilti hollow drill bits:
TE-CD (SDS+)
TE-YD (SDS-max)



 For instructions on how to assemble these systems, please refer to the Hilti North America Youtube page

OSHA 1926.1153 TABLE 1 REQUIREMENTS

These systems fall under OSHA 1926.1153 table 1, **section vii: handheld and stand-mounted drills (including impact and rotary hammer drills)**. In order to be OSHA 1926.1153 table 1 compliant, the below requirements must be met:

- Use drill equipped with commercially available shroud or cowling with dust collection system
- Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions
- Dust collector must provide the air flow recommended by the tool manufacturer, or greater
- Have a filter with 99% or greater efficiency and a filter-cleaning mechanism

Note: Vacuum must be equipped with a HEPA-filter when cleaning holes. No HEPA filter needed when utilizing Hilti hollow drill bits within a Hilti SafeSet system

OSHA 1926.1153 Table 1 states that no respirator is required if the above controls are fully and properly implemented.

Equipment / Task	Engineering and work practice control methods	Required respiratory protections and minimum Assigned Protection Factor (APF)	
		≤ 4 hours / shift	> 4 hours / shift
Handheld and stand-mounted drills (including impact and rotary hammer drills)	Use drill equipped with commercially available shroud or cowling with dust collection system. Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions. Dust collector must provide the air flow recommended by the tool manufacturer, or greater, and have a filter with 99% or greater efficiency and a filter-cleaning mechanism. Use a HEPA-filtered vacuum when cleaning holes.	None	None
		None	None

Check below to see how your system can be compliant with OSHA 1926.1153 Table 1.

Tool models	Accessory	Vacuums (can use any)	Method of compliance
TE 2 series TE 3-C series TE 7 series TE 4-A 22 TE 6-A 36 TE 30 series TE 40-AVR	Any TE-CD drill bit	VC 75-1-A22* VC 125-6 VC 125-9 VC 20-U VC 40-U VC 40-UE VC 150-6 X VC 150-10 X VC 150-6 XE VC 150-10 XE VC 300-17 X	All OSHA 1926.1153 table 1 compliant
TE 50-AVR TE 60 series TE 70 series TE 80-ATC/AVR	Any TE-YD drill bit	VC 75-1-A22* VC 125-6 VC 125-9 VC 20-U VC 40-U VC 40-UE VC 150-6 X VC 150-10 X VC 150-6 XE VC 150-10 XE VC 300-17 X	

*Not approved for SafeSet system.

SYSTEM OVERVIEW

Hilti rotary hammers with a hollow drill bit are OSHA 1926.1153 table 1 compliant through use of a hollowed out drill bit hooked up to a vacuum that meets OSHA 1926.1153 table 1 requirements. Hilti currently offers the below systems with this configuration:

Tool	Accessory	Vacuum (use any)
 <p>TE 2-A 18</p>	 <p>TE-CD hollow drill bits</p>	 <p>VC 75-1-A22*</p>
 <p>TE 2 and TE 2-S</p>		 <p>VC 125-6 VC 125-9</p>
 <p>TE 3-C</p>		 <p>VC 20-U VC 150-6 X</p>
 <p>TE 7 and TE 7-C TE 4-A 22</p>		 <p>VC 150-6 XE VC 40-U</p>
 <p>TE 6-A 36 TE 7-A</p>		 <p>VC 150-10 X VC 40-UE</p>
 <p>TE 30 and TE 30-C TE 30-A 36</p>		 <p>VC 150-10 XE VC 300-17 X</p>

Note: previous generations of tools may have different item numbers or nomenclature. Check with your local Hilti representative or product instruction manual to verify
 *Not approved for SafeSet system.

Tool	Accessory	Vacuum (use any)	
 TE 50-AVR		 VC 75-1-A22*	
 TE 60-A36		 VC 125-6	 VC 125-9
 TE 60-AVR		 VC 20-U	 VC 150-6 X
 TE 60-ATC/AVR	 TE-YD hollow drill bits	 VC 150-6 XE	 VC 40-U
 TE 70-AVR		 VC 150-10 X	 VC 40-UE
 TE 70-ATC/AVR		 VC 150-10 XE	 VC 300-17 X
 TE 80-ATC/AVR			

Note: previous generations of tools may have different item numbers or nomenclature. Check with your local Hilti representative or product instruction manual to verify
 *Not approved for SafeSet system.



HILTI SUBMITTAL PACKAGE OSHA 1926.1153 TABLE 1, SECTIONS vi AND vii

**Section vi: rig-mounted core saws
or drills**

**Section vii: handheld and
stand-mounted drills
(including impact and
rotary hammer drills)**

Current Hilti handheld and rig-mounted core drills

- DD EC-1
- DD 110
- DD 120
- DD 150-U
- DD 160
- DD 200
- DD 250
- DD 350
- DD 500



 For instructions on how to assemble these systems, please refer to the Hilti North America Youtube page

 WMS 100

OSHA 1926.1153 TABLE 1 REQUIREMENTS

These systems fall under either OSHA 1926.1153 table 1, **section vi: handheld and stand-mounted drills (including impact and rotary hammer drills)** or **section vii: handheld and stand-mounted drills (including impact and rotary hammer drills)**. In order to be OSHA 1926.1153 table 1 compliant, the below requirements must be met:

Section vi

- Use tool equipped with integrated water delivery system that supplies water to cutting surface
- Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions

OR

Section vii

- Use drill equipped with commercially available shroud or cowling with dust collection system
- Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions
- Dust collector must provide the air flow recommended by the tool manufacturer, or greater
- Have a filter with 99% or greater efficiency and a filter-cleaning mechanism

OSHA 1926.1153 Table 1 states that no respirator is required if the above controls are fully and properly implemented.

Equipment / Task	Engineering and work practice control methods	Required respiratory protections and minimum Assigned Protection Factor (APF)	
		≤ 4 hours / shift	> 4 hours / shift
(vi) Rig-mounted core saws or drills	<p>Use tool equipped with integrated water delivery system that supplies water to cutting surface.</p> <p>Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions.</p>	None	None
(vii) Handheld and stand-mounted drills (including impact and rotary hammer drills)	<p>Use drill equipped with commercially available shroud or cowling with dust collection system. Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions. Dust collector must provide the air flow recommended by the tool manufacturer, or greater, and have a filter with 99% or greater efficiency and a filter-cleaning mechanism. Use a HEPA-filtered vacuum when cleaning holes.</p>		
	<ul style="list-style-type: none"> • When used outdoors • When used indoors or in an enclosed area 	None	None
		None	None

Check below to see how your system can be compliant with OSHA 1926.1153 Table 1. To verify the generation of your tool, check the rating plate, or call Hilti at 800-879-8000 with your serial number.

Tool name	Accessory (any one)	Method of compliance
DD EC-1 (rig mounted) DD 120 DD 150-U (rig mounted) DD 160 DD 200 DD 250 DD 350 DD 500	DWP 10 (365595) Gardena connector with supplied water (4297) WMS 100 (3575546)	
DD 110 DD 120 DD 150-U DD 160	Any DD-X LM corebit*	Vacuums (can use any) VC 125-6 VC 125-9 VC 20-U VC 40-U VC 40-UE VC 150-6 X VC 150-10 X VC 150-6 XE VC 150-10 XE VC 300-17 X all OSHA 1926.1153 table 1
DD EC-1 handheld DD 110 DD 150-U	DWP 10 (365595) Gardena connector with supplied water (4297) WMS 100 (3575546)	Exposure assessment

*Hilti's interpretation is that dust control core bits with a vacuum are categorized under table 1 section vii: handheld and stand-mounted drills (including impact and rotary hammer drills).

SYSTEM OVERVIEW

Core drills from Hilti comply either through use of a water delivery system or a shrouded core bit hooked up to a Hilti vacuum. Hilti currently offers the below systems with this configuration:

Tool	Accessory
 DD EC-1 (rig mounted)	 DWP 10 handheld water pump
 DD 120	
 DD 150-U (rig mounted)	Any garden connector with a supplied water attached to Hilti tool
 DD 160	
 DD 200	 WMS 100
 DD 250	
 DD 350	
 DD 500	

Note: previous generations of tools may have different item numbers or nomenclature. Check with your local Hilti representative or product instruction manual to verify. OSHA 1926.1153 Table 1 does not address handheld core drills being used wet. For this reason, the only way to comply with handheld wet core drilling is to utilize objective data or exposure assessment procedures.

Tool	Accessory	Vacuum (use any)	
 DD 110-D		 VC 125-6	 VC 125-9
 DD 120		 VC 20-U	 VC 150-6 X
 DD 150-U (handheld)	 Any DD-X LM core drill bit **	 VC 150-6 XE	 VC 40-U
 DD 150-U (rig mounted)		 VC 150-10 X	 VC 40-UE
 DD 160		 VC 150-10 XE	 VC 300-17 X

 DD 110-D*	 DWP 10 handheld water pump		
 DD 150-U (handheld)*	Any gardena connector with a supplied water attached to Hilti tool  WMS 100		

* OSHA 1926.1153 Table 1 does not address handheld core drills being used wet. For this reason, the only way to comply with handheld dry core drilling is to utilize objective data or exposure assessment procedures.

** Hilti interprets dust control coring systems as being in OSHA 1926.1153 table 1, section vii "handheld and stand mounted drills (including impact and rotary hammers)"

CORING — WET

DIA Dust Control — OSHA

Hilti developed diamond coring systems are equipped with a water connection which is to be attached to a pressurized water source. When rig-mounted, these systems are compliant with OSHA 1926.1153, Table 1.

Set-up

1. If required, attach the drill stand to the drilling surface using the appropriate anchoring accessories.
2. Attach the water source to the tool.
3. Insert the bit and ensure its tightened by turning the chuck to the closed position.
4. Turn on the water.
5. Verify you have the appropriate amount of water for the application. Verify the water delivery system operates properly with no leaks, delivering water freely inside the bit.
 - See instructions for core machines.

Drilling

1. Start the water before beginning to drill.
2. Begin drilling, applying the required amount of pressure.
3. Adjust water flow rate to minimize visible dust.

Cleaning and maintenance

- See instructions for core rigs.

Clean-up of slurry before it dries can help minimize secondary exposure. Ensure that cleanup and disposal of concrete slurry is done in accordance with relevant state/local regulations.

CORING — DRY CORING

DIA Dust Control — OSHA

Hilti developed dry diamond core drills and bits to be attached to a Hilti vacuum with a filter cleaning mechanism and 99% filter efficiency. Hilti considers these coring applications to fit in, and be in compliance with, OSHA 1926.1153, Table 1, (vii) handheld and stand-mounted drills (including impact and rotary hammer drills).

Set-up

1. If using as rig-mounted, attach the drill stand to the drilling surface using the appropriate anchoring accessories.
2. Attach the vacuum hose to the drill's vacuum hose connector.
3. Insert the bit and ensure its tightened by turning the chuck to the closed position.
4. Start vacuum.
5. Verify proper operation of the dust collection system, including suction at the end of the bit.
 - Check for damage or leaks in the vacuum, hose, and hose connector.
 - See instructions for vacuum.

Drilling

1. Start the vacuum before beginning to drill.
2. Begin drilling, applying the required amount of pressure.
3. To maximize dust collection, after the hole is drilled, slowly withdraw bit from the hole, and keep the drill and vacuum running until the bit is fully withdrawn.

Cleaning and maintenance

- See instructions for vacuum.



HILTI SUBMITTAL PACKAGE OSHA 1926.1153 TABLE 1, SECTION X

Jackhammers and handheld powered chipping tools

Current Hilti breakers with dust control solutions:

TE 300-A 36 (DRS-C)

TE 500 (DRS-B)

TE 500-AVR (DRS-B)

TE 700-AVR (DRS-B)

TE 800-AVR (DRS-B)

TE 1000-AVR (DRS-B)

TE 1500-AVR (DRS-B)

TE 2000 (DRS-B)

TE 3000-AVR (DRS 3000)



For instructions on how to assemble these systems, please refer to the Hilti North America Youtube page



DRS-B

OSHA 1926.1153 TABLE 1 REQUIREMENTS

These systems fall under OSHA 1926.1153 Table 1, **section x: jackhammers and handheld powered chipping tools**. In order to be OSHA 1926.1153 Table 1 compliant, the below requirements must be met:

- Use tool with water delivery system that supplies a continuous stream or spray of water at the point of impact

or

- Use tool equipped with commercially available shroud or cowl with dust collection system
- Operate and maintain tool in accordance with manufacturer's instructions to minimize dust emissions
- Dust collector must provide the air flow recommended by the tool manufacturer, or greater
- Have a filter with 99% or greater efficiency and a filter-cleaning mechanism

OSHA 1926.1153 Table 1 requires a respirator to be worn in certain environments based on the time of the application. Check below to see when an APF 10 respirator must be worn.

Equipment / Task	Engineering and work practice control methods	Required respiratory protections and minimum Assigned Protection Factor (APF)	
		≤ 4 hours / shift	> 4 hours / shift
(x) Jackhammers and handheld powered chipping tools	Use tool with water delivery system that supplies a continuous stream or spray of water at the point of impact. <ul style="list-style-type: none"> • When used outdoors • When used indoors or in an enclosed area 	None	APF 10
		APF 10	APF 10
OR			
	Use tool equipped with commercially available shroud and dust collection system. Operate and maintain tool in accordance with manufacturer's instructions to minimize dust emissions. Dust collector must provide the air flow recommended by the tool manufacturer, or greater, and have a filter with 99% or greater efficiency and a filter-cleaning mechanism. <ul style="list-style-type: none"> • When used outdoors • When used indoors or in an enclosed area 	None	APF 10
		APF 10	APF 10

Check below to see how your system can be compliant with OSHA 1926.1153 Table 1. To verify the generation of your tool, check the rating plate, or call Hilti at 800-879-8000 with your serial number. To check fit of the DRS-B with older tool generations, check the sticker on the inside of the case on the DRS-B, or refer to the instruction manual.

Tool models	Accessory	Vacuums (can use any)	Method of compliance
TE 300-A36 TE 50 / 56 / 60 / 70 / 76 / 80 TE 500 / TE 505 / 500-AVR TE 706 / 700-AVR TE 805 / TE 800-AVR TE 905 TE 1000-AVR TE 1500-AVR TE 2000	DRS-C Item number: 2213351 DRS-B Item number 365944	VC 75-A22 VC 125-6 VC 125-9 VC 20-U VC 40-U VC 40-UE VC 150-6 X VC 150-10 X VC 150-6 XE VC 150-10 XE VC 300-17 X	All OSHA 1926.1153 table 1 compliant
TE 3000-AVR	DRS 3000 Item number 2171779		

SYSTEM OVERVIEW

Hilti combihammers, hammers, and breakers are OSHA 1926.1153 Table 1 compliant through use of a dust collection shroud hooked up to a vacuum that meets OSHA 1926.1153 Table 1 requirements. Hilti currently offers the below systems with this configuration:

Tool	Accessory	Vacuum (use any)
 <p>TE 300 A36</p>	 <p>DRS-C</p>	 <p>VC 75-1-A22*</p>
 <p>TE 500 & TE 500-AVR</p>		  <p>VC 125-6</p> <p>VC 125-9</p>
 <p>TE 700-AVR</p>		  <p>VC 20-U</p> <p>VC 150-6 X</p>
 <p>TE 800-AVR</p>	 <p>TE DRS-B</p>	  <p>VC 150-6 XE</p> <p>VC 40-U</p>
 <p>TE 1000-AVR</p>		  <p>VC 150-10 X</p> <p>VC 40-UE</p>
 <p>TE 2000-AVR</p>		  <p>VC 150-10 XE</p> <p>VC 300-17 X</p>
 <p>TE 3000-AVR</p>	 <p>TE DRS 3000</p>	

Note: previous generations of tools may have different item numbers or nomenclature. Check with your local Hilti representative or product instruction manual to verify
 *If a decrease in suction occurs with the VC 75-1-A22, Hilti's manufacturer guidelines recommends pushing the filter cleaning button on the tool to clear the filter.



HILTI SUBMITTAL PACKAGE OSHA 1926.1153 TABLE 1, SECTION XI AND XII

**Sections xi: Handheld grinders for
mortar removal**

**Section xii: Handheld grinders for
uses other than
mortar removal**

Current Hilti angle grinders with a Hilti cutting hood:

- AG 450-7S
- AG 450-7D
- AG 4S-A22
- DEG 500
- DAG 500-D
- DCG 500-S
- AG 500-11S
- AG 500-12D
- DCH 230
- DCH 300-X



For instructions on how to assemble these systems, please refer to the Hilti North America Youtube page



DCH



Angle grinders with a cutting hood

OSHA 1926.1153 TABLE 1 REQUIREMENTS

These systems fall under OSHA 1926.1153 table 1, **section xi: handheld grinders for mortar removal**; and **section xii: handheld grinders for use other than mortar removal**. In order to be OSHA 1926.1153 table 1 compliant, the below requirements must be met:

- When performing non-mortar removal applications outside: use a grinder equipped with integrated water delivery system that continuously feeds water to the grinding surface

or

- Use tool equipped with commercially available shroud or cowling with dust collection system
- Operate and maintain tool in accordance with manufacturer's instructions to minimize dust emissions
- Dust collector must provide the air flow recommended by the tool manufacturer, or greater
- Have a filter with 99% or greater efficiency and a filter-cleaning mechanism
- Dust collector must provide 25 cubic feet per minute (cfm) or greater of airflow per inch of wheel diameter

OSHA 1926.1153 Table 1 requires a respirator to be worn in certain environments based on the time of the application. Check below to see when an APF 10 or APF 25 respirator must be worn.

Equipment / Task	Engineering and work practice control methods	Required respiratory protections and minimum Assigned Protection Factor (APF)	
		≤ 4 hours / shift	> 4 hours / shift
(xi) Handheld grinders for mortar removal (i.e., tuckpointing)	<p>Use grinder equipped with commercially available shroud and dust collection system.</p> <p>Operate and maintain tool in accordance with manufacturer's instructions to minimize dust emissions.</p> <p>Dust collector must provide 25 cubic feet per minute (cfm) or greater of airflow per inch of wheel diameter and have a filter with 99% or greater efficiency and a cyclonic pre-separator or filter-cleaning mechanism.</p>	APF 10	APF 25
(xii) Handheld grinders for use other than mortar removal	<p>For tasks performed outdoors only.</p> <p>Use grinder equipped with integrated water delivery system that continuously feeds water to the grinding surface.</p> <p>Operate and maintain tool in accordance with manufacturer's instructions to minimize dust emissions.</p> <p>OR</p> <p>Use grinder equipped with commercially available shroud and dust collection system.</p> <p>Operate and maintain tool in accordance with manufacturer's instructions to minimize dust emissions.</p> <p>Dust collector must provide 25 cubic feet per minute (cfm) or greater of airflow per inch of wheel diameter and have a filter with 99% or greater efficiency and a cyclonic pre-separator or filter-cleaning mechanism.</p>	None	None
	<ul style="list-style-type: none"> • When used outdoors 	None	None
	<ul style="list-style-type: none"> • When used indoors or in an enclosed area 	None	APF 10

Check below to see how your system can be compliant with OSHA 1926.1153.

Tool models	Accessory	Vacuums (can use any)	Method of compliance
AG 450-7S AG 450-7D AG 4S-A22 AG 500 7SE	Dust guard cutting (Item number 2101312)	VC 125-6 VC 125-9 VC 20-U VC 40-U VC 40-UE VC 150-6 X VC 150-10 X VC 150-6 XE VC 150-10 XE VC 300-17 X	OSHA 1926.1153 Table 1 compliant
DEG 500 DCG 500-S DAG 500-D AG 500-11S AG 500-12D AG 500 A22	Dust guard cutting (Item number 284978) or Dust guard slitting (Item number 267720)	VC 300-17 X	OSHA 1926.1153 Table 1
DCH 230**	Depth gauge DCH 230 (Item number 212187) Slitting adapter DCH 230 / 180-SL (Item number 212253)	VC 125-6 VC 125-9 VC 20-U VC 40-U VC 40-UE VC 150-6 X VC 150-10 X VC 150-6 XE VC 150-10 XE	Exposure assessment Objective data*
DCH 300-X**	Depth gauge DCH 300/300-X (Item number 212131)	VC 300-17 X VC 125-6 VC 125-9 VC 20-U VC 40-U VC 40-UE VC 150-6 X VC 150-10 X VC 150-6 XE VC 150-10 XE	OSHA 1926.1153 Table 1 Exposure assessment Objective data*
DCH 300-X	Depth gauge (Item number 212131) DWP 10 (Item number 365595) Gardena connector with supplied water (Item number 4297)	-	OSHA 1926.1153 Table 1 compliant

*See Hilti's published Objective Data — if not applicable to a specific application, exposure assessment is required.

** Hilti interprets the DCH 230/300 as a section xii: handheld grinder for other than mortar removal.

SYSTEM OVERVIEW

Hilti concrete cutting tools are OSHA 1926.1153 table 1 compliant for both mortar removal and non-mortar removal applications through use of a dust collection shroud hooked up to a vacuum that meets OSHA 1926.1153 table 1 requirements. Hilti currently offers the below systems with this configuration. The handheld DCH 300-X electric saw complies with OSHA 1926.1153 Table 1 through both a dust collection shroud connected to a vacuum or a integrated water delivery system to supply water to the cutting surface.

Tool	Accessory	Vacuum (use any)		
 AG 450-7S	 4-1/2" cutting hood	 VC 125-6	 VC 125-9	
 AG 450-7D				
 AG 500-7SE				
 AG 4S-A22			 VC 20-U	 VC 150-6 X
 DEG 500	 5" cutting hood	 VC 150-6 XE	 VC 40-U	
 DCG 500-S			 VC 150-10 X	 VC 40-UE
 DAG 500-D	 5" slitting hood	 VC 150-10 XE	 VC 300-17 X	
 AG 500 A22				
 AG 500-11S				
 AG 500-11D				
 AG 600-A36				

Note: previous generations of tools may have different item numbers or nomenclature. Check with your local Hilti representative or product instruction manual to verify

Tool	Accessory	Vacuum (use any)	
 <p>DCH 230 ***</p>	 <p>Depth gauge</p>  <p>Slitting adapter DCH 230 / 180-SL</p>	 <p>VC 125-6*</p>  <p>VC 20-U**</p>  <p>VC 150-6 XE**</p>	 <p>VC 125-9*</p>  <p>VC 150-6 X**</p>  <p>VC 40-U**</p>
 <p>DCH 300-X***</p>	 <p>Depth gauge</p>	 <p>VC 150-10 X**</p>  <p>VC 150-10 XE**</p>	 <p>VC 40-UE**</p>  <p>VC 300-17 X***</p>
 <p>DCH 300-X</p>	 <p>Depth gauge</p>  <p>DWP 10 handheld water pump</p>		

*Exposure assessment required

**See Hilti's published Objective Data — if not applicable to a specific application, exposure assessment is required.

*** Hilti interprets the DCH 230/300 as a section xii "handheld grinder for other than mortar removal".

Note: previous generations of tools may have different item numbers or nomenclature. Check with your local Hilti representative or product instruction manual to verify



OSHA 29 CFR §1926.1153
Respirable Silica Dust Exposure
Objective Test Data

Hilti DCH 230-300, depth gauge, VC 20-U/40-U/40-UE vacuum

Hilti has performed testing of the above system to determine the operator's respirable silica dust exposure in accordance with EN 50632-1 and EN 50632-2-22. Testing was performed under the following conditions:

- Room size: 7.8m x 7.8m x 3.3m (200 m³). Closed – no air exchange.
- Cutting disc: EQD SPX.
- Test duration: 1 hour.
- Cutting depth: 40 mm.
- Cutting length: 45 feet.
- Cutting orientation: horizontal down, approx. 3 ft above floor level.
- Force applied: average 70-90% of tool rated amperage.
- Base material: concrete.
- Sampler: 10 l/min GSP pump, FSP sampler. ISO 7708-compliant. 5 µm filter.
- Air sample volume collected during test: 600 liters.

Results:

Time-Weighted Average Respirable Silica Dust Exposure ^{1,2}	327 µg/m ³
--	-----------------------



The 8-hour TWA is 41 µg/m³ if working one hour @ 327 µg/m³ (1-hour TWA), and no further exposure occurs throughout the shift.

¹ The silica content of base materials varies. As a result, the silica content in respirable dust samples also varies. The above-published exposure value is based on a 20% silica content applied to the total respirable dust measurement. Measured average silica content during testing was 15.5%.

² Exposure value represents the time-weighted average (TWA) over the 1-hour test period. Due to the test being conducted in a closed, non-ventilated room, this TWA exposure value would increase if the test duration was extended under the same conditions.



29 CFR §1926.1153(d)(2)(ii)
Performance Option

How to utilize Hilti “Objective Data”

Hilti has conducted testing to establish the respirable silica dust exposure (“exposure level”), associated with the use of various Hilti tool systems. These tests were performed in accordance with EN 50632, except the specific work configuration may vary to provide more versatile data and better address U.S. practices. The purpose of the testing was to generate “Objective Data” to be used as part of the exposure assessment requirements of 29 CFR §1926.1153(d)(2)(ii).

Per the EN standard, testing was performed for 1 hour in a 200m³ closed, non-ventilated room. Under these conditions, exposure levels increase over time. The exposure values published in Hilti’s Objective Data represent the average over the 1-hour test period (1-hour TWA)¹. Meaning the TWA started at zero, rose to the published 1-hour value, and would continue to rise if the test were continued.

Several underlying concepts important to applying the Objective Data to any case-specific assessment:

1. More/less work performed in a given time period will increase/decrease the exposure level.
2. Larger/smaller room size will decrease/increase the exposure level.
3. Air exchange decreases exposure levels. Specifically, a 100% air-exchange every hour (either by the work moving to a discrete area, or via sufficient air movement), means Hilti’s published 1-hour TWA exposure level is expected to conservatively represent a steady-state TWA. The conceptual basis is two-fold: air exchange would inherently reduce the published “closed room” exposure value. And sufficient air exchange to “reset” the environment every hour would keep the exposure values at that level. For reference, a typical 20”, 2500 CFM box fan would introduce 100% new air volume in Hilti’s test chamber (7,200 ft³), every 3 minutes².
4. The OSHA 50 µg/m³ Permissible Exposure Level (PEL), is based on an 8-hour TWA. This means the exposure level as an 8-hour TWA is ≤50 µg/m³; a 4-hour TWA is ≤100 µg/m³ (assuming no exposure for the remainder of the shift); a 2-hour TWA is ≤200 µg/m³ (assuming no exposure for the remainder of the shift) etc. (time [hours] x exposure level [µg/m³] ≤ 400).

Hilti’s published Objective Data states the amount of work performed during the 1-hour test (“1-hour work”). Therefore, the respirable silica dust exposure level in any case-specific situation is expected to be below the 8-hour TWA PEL in the following conditions³:

- An employee performing ≤ “1-hour work” during a shift.
- An employee performing ≤ “1-hour work” in an hour, then moving to another discrete area and performing ≤ “1-hour work” in an hour, etc., throughout an entire shift.
- An employee performing ≤ “1-hour work” each hour, in an environment with sufficient air-exchange to prevent accumulation of airborne dust.

¹ Hilti’s published Objective Data incorporates a silica content of 20% of the total respirable dust measurement. Site-specific silica content varies. OSHA Docket No. OSHA-2010-0034, reviewed 588 respirable dust samples from construction tasks, finding the silica content varied from <1%-50%, with an average of 9.1%.

² Note introduction/exhaust of 100% air volume does not necessarily correlate to a 100% air exchange.

³ As long as: (1) Hilti’s published Objective Data exposure level is ≤50 µg/m³; (2) work is performed in a room with volume ≥ 200m³, and/or having adequate ventilation; and (3) site-specific respirable silica content is ≤20% of total respirable dust.

DCH 300/230

Presentation

Hilti developed DCH 300(X)/230 tool which could be connected to a vacuum cleaner to collect dust (which Hilti interprets to be compliant with OSHA 1926.1153, table 1 “hand-held grinder using a vacuum cleaner with at least 25 cfm per inch of the wheel diameter and a filter cleaning mechanism with an efficiency of 99% or greater)

Set-up

1. When cutting mineral materials, use a suitable vacuum cleaner (eg. Hilti VC 300) with the corresponding filter
2. Attach the depth gauge (DCH 300(X) = #212131/DCH 230 = #212187) to DCH tools with the desired depth of cut. Always keep the depth gauge in full contact with the base material when cutting
3. Connect vacuum cleaner hose to respective opening in DCH 300(X)/DCH 230 blade guard
4. Connect the tool to a suitable electric power source
5. Adjust the depth/ cut in steps of max. 40-50mm
6. Switch vacuum cleaner on first then switch DCH 300(X)/DCH 230 on and start cutting
7. Start cut by placing front of tool on base material, and then pivoting back of tool into the cut. Always keep front of tool in contact with base material.
8. Verify proper operation => Check for damage or leakage at tool, hose to connection of both. Ensure tool disc guard and exhaust port are free of obstruction.
9. When cut is finished, release trigger of DCH and allow to stop before removing from cut
10. Keep vacuum running until cutting is completed
11. The following will increase dust exposure — minimize these activities:
 - through cutting
 - cutting past the end of the base material
 - making multiple passes for a cut
 - pulling the DCH toward you to cut
 - attempting to angle the disc at other than a perpendicular cut into the base material

Application

- Electric powered cutter for the construction industry
- Design to for cutting mineral material with Diamond blades without use of water
- With synthetic resin-bonded fibre-reinforced abrasive disc discs the tools could be also used to cut metal (not connected to vacuum cleaner)

HILTI ANGLE GRINDERS WITH A CONCRETE CUTTING HOOD

Presentation

Hilti developed various angle grinders for mortar removal and other cutting applications. When configured with the correct guard/hood and connected to the appropriate vacuum, these tools are compliant with OSHA 1926.1153 Table 1 (xi) “handheld grinders for mortar removal (i.e., tuckpointing)” or (xii) “handheld grinders for uses other than mortar removal” (note Hilti interprets the DCH 230/300(X) to be a “handheld grinder”). For OSHA 1926.1153 Table 1 compliance, the vacuum cleaner must have at least 25 cfm per inch of the wheel diameter, a filter cleaning mechanism, and a filter efficiency of at least 99%.

Set-up

1. When cutting mineral materials, use a suitable vacuum cleaner (eg. Hilti VC 300(X)) with the corresponding filter
2. Attach the guard/hood/depth gauge (see submittal package for appropriate item number) to the tool with the desired depth of cut. Always keep the depth gauge in full contact with the base material when cutting
3. Connect vacuum cleaner hose to respective opening in grinder blade guard
4. Connect the tool to a suitable electric power source
5. Adjust the depth/ cut in steps of max. 40-50mm
6. Switch vacuum cleaner on first then switch grinder on and start cutting
7. If setup properly, the blade will rotate toward the vacuum collection port. The end of the guard with the vacuum port must always be placed against the concrete first. Always pull or push the tool in the direction of the vacuum port.
8. Verify proper operation => Check for damage or leakage at tool, hose to connection of both. Ensure tool disc guard and exhaust port are free of obstruction.
9. When cut is finished, release trigger of tool and allow to stop before removing from cut
10. Keep vacuum running until cutting is completed
11. The following will increase dust exposure — minimize these activities:
 - through cutting
 - cutting past the end of the base material
 - making multiple passes for a cut
 - pulling/pushing the tool in a direction opposite the vacuum port
 - attempting to angle the disc at other than a perpendicular cut into the base material

Application

- Electric powered angle grinders/cutters for the construction industry
- Design to for cutting mineral material with Diamond blades without use of water
- With synthetic resin-bonded fibre-reinforced abrasive disc discs the tools could be also used to cut metal (not connected to vacuum cleaner)



HILTI SUBMITTAL PACKAGE OSHA 1926.1153 TABLE 1, SECTION ii

Section ii: handheld power saws (any blade diameter)

Current Hilti saws with wet cutting solutions

DSH 600-X

DSH 700-X

DSH 900-X



For instructions on how to assemble these systems, please refer to the Hilti North America Youtube page



DSH saws + DSH-P

OSHA 1926.1153 TABLE 1 REQUIREMENTS

These systems fall under OSHA 1926.1153 Table 1, **section ii: handheld power saws (any blade diameter)**. In order to be OSHA 1926.1153 table 1 compliant, the below requirements must be met:

- Use saw equipped with integrated water delivery system that continuously feeds water to the blade.
- Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions.

Equipment / Task	Engineering and work practice control methods	Required respiratory protections and minimum Assigned Protection Factor (APF)	
		≤ 4 hours / shift	> 4 hours / shift
(ii) handheld power saws (any blade diameter)	Use saw equipped with integrated water delivery system that continuously feeds water to the blade.	None	APF 10
	Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions.		
	<ul style="list-style-type: none"> • When used outdoors 	APF 10	APF 10
	<ul style="list-style-type: none"> • When used indoors or in an enclosed area 	APF 10	APF 10

OSHA 1926.1153 Table 1 states when a respirator is required if the above controls are fully and properly implemented.

Check below to see how your system can be compliant with OSHA 1926.1153 Table 1. To verify the generation of your tool, check the rating plate, or call Hilti at 800-879-8000 with your serial number.

Tool name	Accessory (any one)	Method of compliance
DSH 600-X DSH 700 series DSH 900 series	DSH-P water pump (2124505) DWP 10 (365595) Gardena connector with supplied water (4297) DSH-FSC Floor Saw Cart (431364)	OSHA 1926.1153 Table 1

SYSTEM OVERVIEW

Handheld power saws from Hilti comply with OSHA 1926.1153 Table 1 through an integrated water delivery system to supply water to the cutting surface. Hilti currently offers the below systems with this configuration:

Tool	Accessory
 <p data-bbox="272 806 370 827">DSH 600-X</p>	 <p data-bbox="721 674 899 695">DSH-P water pump</p>
 <p data-bbox="272 1052 370 1073">DSH 700-X</p>	 <p data-bbox="678 978 943 999">DWP 10 handheld water pump</p>
 <p data-bbox="272 1293 370 1314">DSH 900-X</p>	<p data-bbox="607 1073 1013 1115">Any "Gardena" style connector can be used to attach the water source to the Hilti gas saw</p>  <p data-bbox="704 1398 915 1419">DSH-FSC floor saw cart</p>

Note: previous generations of tools may have different item numbers or nomenclature. Check with your local Hilti representative or product instruction manual to verify.

DSH 600-X/700-X/900-X

DSH Handheld Gas Saw Dust Control – OSHA

Hilti developed gas saw cutting systems which are equipped with a water connection to be attached to a pressurized water source, compliant with OSHA 1926.1153, Table 1. The use of the Hilti DSH-P eliminates the need for a pressurized water source.

Set-up

1. Attach the water source to the tool.
2. Turn on the water.
3. Verify that the user has the appropriate supply of water, and that the gas saw's water valve functions properly.
4. See DSH gas saw operator's instructions for additional information
 - Check for damage or leaks in the DSH gas saw's valve and water tube.
 - Verify the spray nozzles are not clogged, and direct the water to the cutting surface.

Cutting

1. Turn on the pressurized water source before beginning to cut.
 - Adjust the water valve to ensure proper water flow during cutting to minimize visible dust.
2. Maintain water flow until cutting is completed.

Cleaning and maintenance

- See manufacturer's instructions for wet cutting machines



HILTI SUBMITTAL PACKAGE OSHA 1926.1153 TABLE 1, SECTION xii

Sections xii: Handheld grinders for uses other than mortar removal

Current Hilti angle grinders with a Hilti grinding hood:

AG 450-7S
AG 450-7D
AG 4S-A22
DEG 500
DAG 500-D
DCG 500-S
AG 500-11S
AG 500-12D
AG 500 7SE
AG 500 A22
DGH 130
DG 150
AG 700-14D



For instructions on how to assemble these systems, please refer to the Hilti North America Youtube page



DG 150



Angle grinders with a grinding hood

OSHA 1926.1153 TABLE 1 REQUIREMENTS

These systems fall under OSHA 1926.1153 table 1, **section xii: handheld grinders for use other than mortar removal**. In order to be OSHA 1926.1153 table 1 compliant, the below requirements must be met:

- When performing outdoor applications only: use a grinder equipped with integrated water delivery system that continuously feeds water to the grinding surface

or

- Use tool equipped with commercially available shroud or cowling with dust collection system
- Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions
- Dust collector must provide the air flow recommended by the tool manufacturer, or greater
- Have a filter with 99% or greater efficiency and a filter-cleaning mechanism
- dust collector must provide 25 cubic feet per minute (cfm) or greater of airflow per inch of wheel diameter

OSHA 1926.1153 Table 1 requires a respirator to be worn in certain environments based on the time of the application. Check below to see when an APF 10 respirator must be worn.

Equipment / Task	Engineering and work practice control methods	Required respiratory protections and minimum Assigned Protection Factor (APF)	
		≤ 4 hours / shift	> 4 hours / shift
(xii) Handheld grinders for uses other than mortar removal	For tasks performed outdoors only. Use grinder equipped with integrated water delivery system that continuously feeds water to the grinding surface. Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions. OR Use grinder equipped with commercially available shroud and dust collection system. Operate and maintain tool in accordance with manufacturer’s instructions to minimize dust emissions. Dust collector must provide 25 cubic feet per minute (cfm) or greater of airflow per inch of wheel diameter and have a filter with 99% or greater efficiency and a cyclonic pre-separator or filter-cleaning mechanism.	None	None
	• When used outdoors	None	None
	• When used indoors or in an enclosed area	None	APF 10







Check below to see how your system can be compliant with OSHA 1926.1153 Table 1. To verify the generation of your tool, check the rating plate, or call Hilti at 800-879-8000 with your serial number.

Tool models	Accessory	Vacuums (can use any)	Method of compliance
AG 450-7S AG 450-7D AG 4S-A22 AG 500 7SE	Dust guard grinding hoods (Item number 2102983)	VC 125-6 VC 125-9 VC 20-U VC 40-U VC 40-UE	OSHA 1926.1153 Table 1 compliant
DEG 500 DCG 500-S DAG 500-D AG 500-11S AG 500-12D AG 500 A22	Dust guard grinding hoods (Item number 267719 or Item number 2126539)	VC 150-6 X VC 150-10 X VC 150-6 XE VC 150-10 XE VC 300-17 X	
AG 600-A 36 grinding hoods for AG 600 are designed for 5 inch max. diameter wheels only	Dust guard grinding hoods (Item number 267719 or Item number 2126539)	VC 150-6 X VC 150-10 X VC 150-6 XE VC 150-10 XE VC 300-17 X VC 125-6 VC 125-9	OSHA 1926.1153 Table 1 compliant
AG 700-14D	Dust extr. hood DG-EX 180//7" grinding	VC 300-17 X	OSHA 1926.1153 Table 1 compliant
DGH 130	no adapter needed	VC 20-U VC 40-U VC 40-UE VC 150-6 X VC 150-10 X VC 150-6 XE VC 150-10 XE VC 300-17 X	OSHA 1925.1153 Table 1 compliant
DG 150	Vacuum adapter (Item number 281862)	VC 300-17 X	OSHA 1926.1153 Table 1 compliant
		VC 150-6 X VC 150-10 X VC 150-6 XE VC 150-10 XE	OSHA 1926.1153 Table 1 compliant / Objective data*
		VC 125-6 VC 125-9	Exposure assessment
		VC 20-U VC 40-U VC 40-UE	Objective data*

*See Hilti's published Objective Data — if not applicable to a specific application, exposure assessment is required.

SYSTEM OVERVIEW

Hilti concrete grinding tools are OSHA 1926.1153 table 1 compliant through use of a dust collection shroud hooked up to a vacuum that meets OSHA 1926.1153 table 1 requirements. Hilti currently offers the below systems with this configuration:

Tool	Accessory	Vacuum (use any)		
 AG 450-7S	 4-1/2" grinding hood	 VC 125-6	 VC 125-9	
 AG 450-7D		<hr/>	 VC 20-U	 VC 150-6 X
 AG 4S-A22			 VC 150-6 XE	 VC 40-U
 AG 500-7SE			 VC 150-10 X	 VC 40-UE
 DEG 500	 5" grinding hood		 VC 150-10 XE	 VC 300-17 X
 DCG 500-S		<hr/>	 VC 150-10 XE	 VC 300-17 X
 DAG 500-D			 VC 150-10 XE	 VC 300-17 X
 AG 500-11S			 VC 150-10 XE	 VC 300-17 X
 AG 500-11D	<hr/>	 VC 150-10 XE	 VC 300-17 X	
 AG 500-11D		 VC 150-10 XE	 VC 300-17 X	
 AG 500-A22	<hr/>	 VC 150-10 XE	 VC 300-17 X	

Note: previous generations of tools may have different item numbers or nomenclature. Check with your local Hilti representative or product instruction manual to verify

Tool	Accessory	Vacuum (use any)
 <p>AG 600-A 36 grinding hoods for AG 600 are designed for 5 inch max. diameter wheels only</p>	 <p>5" grinding hood</p>	 <p>VC 125-6</p>  <p>VC 125-9</p>  <p>VC 150-6 XE</p>  <p>VC 150-6 X</p>  <p>VC 150-10 X</p>  <p>VC 150-10 XE</p>  <p>VC 300-17 X</p>
 <p>AG 700-14D</p>	 <p>Dust extr. hood DG-EX 180//7" grinding</p>	 <p>VC 300-17 X</p>

*Exposure assessment required

**See Hilti's published Objective Data — if not applicable to a specific application, exposure assessment is required.

*** OSHA 1926.1153 Table 1 compliant, with the option to use objective data test report

Tool	Accessory	Vacuum (use any)	
 <p>DGH 130</p>	-	 <p>VC 150-6 XE</p>  <p>VC 150-10 X</p>  <p>VC 300-17 X</p>	 <p>VC 150-6 X</p>  <p>VC 150-10 XE</p>
 <p>DG 150</p>	 <p>Vacuum adapter</p>	 <p>VC 125-6*</p>  <p>VC 20-U**</p>  <p>VC 150-6 XE***</p>  <p>VC 150-10 X***</p>  <p>VC 150-10 XE***</p>	 <p>VC 125-9*</p>  <p>VC 150-6 X***</p>  <p>VC 40-U**</p>  <p>VC 40-UE**</p>  <p>VC 300-17 X</p>

*Exposure assessment required

**See Hilti's published Objective Data — if not applicable to a specific application, exposure assessment is required.

*** OSHA 1926.1153 Table 1 compliant, with the option to use objective data test report

OSHA 29 CFR §1926.1153
Respirable Silica Dust Exposure
Objective Test Data – Grinding
Hilti DG 150 with VC20-U/40-U/40-UE vacuum

Hilti has performed testing of the above system to determine the operator’s respirable silica dust exposure in accordance with EN 50632-1 and EN 50632-2-3. Testing was performed under the following conditions:

- Room size: 7.8m x 7.8m x 3.3m (200 m³). Closed – no air exchange.
- Grinding disc: DG-CW 150/6” CR-SP
- Test duration: 1 hour.
- Weight of collected dust: 1590 g.
- Grinding orientation: 15° from vertical.
- Grinding height: 2’-6’ above floor-level.
- Force applied: average 70-90% of tool rated amperage.
- Base material: concrete slab.
- Sampler: 10 l/min GSP pump, FSP sampler. ISO 7708-compliant. 5 µm filter.
- Air sample volume collected during test: 600 liters.

Results:

Time-Weighted Average Respirable Silica Dust Exposure ^{1,2}	43 µg/m ³
--	----------------------



¹ The silica content of base materials varies. As a result, the silica content in respirable dust samples also varies. The above-published exposure value is based on a 20% silica content applied to the total respirable dust measurement. Measured average silica content during testing was 10.0%.

² Exposure value represents the time-weighted average (TWA) over the 1-hour test period. Due to the test being conducted in a closed, non-ventilated room, this TWA exposure value would increase if the test duration was extended under the same conditions.

HOW TO UTILIZE HILTI “OBJECTIVE DATA”

29 CFR §1926.1153(d)(2)(ii)

Performance option

Hilti has conducted testing to establish the respirable silica dust exposure (exposure level), associated with the use of various Hilti tool systems. These tests were performed in accordance with EN 50632, except the specific work configuration may vary to provide more versatile data and better address U.S. practices. The purpose of the testing was to generate “Objective Data” to be used as part of the exposure assessment requirements of 29 CFR §1926.1153(d)(2)(ii).

Per the EN standard, testing was performed for 1 hour in a 200m³ closed, non-ventilated room. Under these conditions, exposure levels increase over time. The exposure values published in Hilti’s Objective Data represent the average over the 1-hour test period (1-hour TWA)¹. Meaning the TWA started at zero, rose to the published 1-hour value, and would continue to rise if the test were continued.

There are several underlying concepts important to applying the Objective Data to any case-specific assessment:

1. More/less work performed in a given time period will increase/decrease the exposure level.
2. Larger/smaller room size will decrease/increase the exposure level.
3. Air exchange decreases exposure levels. Specifically, a 100% air-exchange every hour (either by the work moving to a discrete area, or via sufficient air movement), means Hilti’s published 1-hour TWA exposure level is expected to conservatively represent a steady-state TWA. The conceptual basis is two-fold: air exchange would inherently reduce the published “closed room” exposure value. And sufficient air exchange to “reset” the environment every hour would keep the exposure values at that level. For reference, a typical 20”, 2500 CFM box fan would introduce 100% new air volume in Hilti’s test chamber (7,200 ft³), every 3 minutes².
4. The OSHA 50 µg/m³ Permissible Exposure Limit (PEL), is based on an 8-hour TWA. This means the exposure level as an 8-hour TWA is ≤50 µg/m³; a 4-hour TWA is ≤100 µg/m³ (assuming no exposure for the remainder of the shift); a 2-hour TWA is ≤200 µg/m³ (assuming no exposure for the remainder of the shift) etc. (time [hours] x exposure level [µg/m³] ≤ 400).

Hilti’s published Objective Data states the amount of work performed during the 1-hour test (“1-hour work”). Therefore, the respirable silica dust exposure level in any case-specific situation is expected to be below the 8-hour TWA PEL in the following conditions³:

- An employee performing ≤ “1-hour work” during a shift.
- An employee performing ≤ “1-hour work” in an hour, then moving to another discrete area and performing ≤ “1-hour work” in an hour, etc., throughout an entire shift.
- An employee performing ≤ “1-hour work” each hour, in an environment with sufficient airexchange to prevent accumulation of airborne dust.

¹ Hilti’s published Objective Data incorporates a silica content of 20% of the total respirable dust measurement. Site-specific silica content varies. OSHA Docket No. OSHA-2010-0034, reviewed 588 respirable dust samples from construction tasks, finding the silica content varied from <1%-50%, with an average of 9.1%.

² Note introduction/exhaust of 100% air volume does not necessarily correlate to a 100% air exchange.

³ As long as: (1) Hilti’s published Objective Data exposure level is ≤50 µg/m³; (2) work is performed in a room with volume ≥ 200m³, and/or having adequate ventilation; and (3) site-specific respirable silica content is ≤20% of total respirable dust.

GRINDING

Grinding Dust Control – OSHA

Hilti developed dust collection systems for its angle grinders with a shroud, to be attached to a Hilti vacuum with a filter cleaning mechanism and 99% filter efficiency, compliant with OSHA 1926.1153, Table 1.

Set-up

1. Attach the appropriate dust collection shroud to the grinder.
2. Select appropriately-sized vacuum (per OSHA 1926.1153 Table 1, the vacuum must have a rating of at least 25 cfm per inch of wheel diameter). Attach vacuum hose to grinder shroud.
3. Start vacuum.
4. Verify proper operation of the dust collection system, including suction at the shroud
 - Check for damage or leaks in the vacuum, hose, and shroud.
 - See instructions for vacuum.
5. Verify the shroud seal is intact, and extends to at least the face of the cup wheel.

Grinding

1. Start the vacuum before beginning to grind.
2. Hold the cup wheel face parallel with (flat to) the work surface. Always maintain the grinder such that the shroud seal is in full contact with the work surface (i.e., do not tilt the grinder)
3. Avoid grinding over a free edge of the work surface as much as possible.
 - shrouds can be opened slightly to allow close access to a perpendicular obstruction. Only operate in this opened condition when necessary.
4. Release the tool trigger and allow the grinder to come to a complete stop before lifting it from the work surface. Keep vacuum running until grinding operation is completed.

Cleaning and maintenance

- See instructions for vacuum.



HILTI VACUUM PORTFOLIO

Supporting information



 For instructions on how to assemble these systems, please refer to the Hilti North America Youtube page

 VC 75

 VC 125

 VC 150

 VC 300

CONTENTS

Statements of compliance.62-64
Vacuum Test Reports	65-74
HEPA certification for VC 20, 40 series vacuums	75-77
HEPA Certification for VC 75-A2278
HEPA certification for VC 125, 150, and 300 series vacuums	79-85
Supplemental instructions.	86-90



April 16, 2019

Statement on features of Hilti VC 75-1-A22 series vacuum:

Regarding OSHA 29 CFR Part 1926 §1153, please note that the Hilti VC 75-1-A22 vacuum meets the following requirements given in Table 1:

- **99% or greater filter efficiency**
- **Manual filter mechanism**
- **Provides 75 cfm**
- **A HEPA filter is available**

When used in conjunction with the corresponding Hilti tools and dust removal systems meeting the listed Table 1 requirements, the user will have a compliant system as specified in the regulation.

Please contact your local Hilti representative with any additional questions. For additional clarification, please refer to 29 CFR Part 1926 §1153.

Sincerely,

Hilti product team

Hilti, Inc.
7250 Dallas Parkway, Ste 1100
Plano, TX 75024

1-800-879-8000
www.hilti.com



June 23, 2017

Statement on features of Hilti VC 125 series vacuums:

Regarding OSHA 29 CFR Part 1926 §1153, please note that the Hilti 125-6 and 125-9 vacuums all meet the following requirements given in Table 1:

- **99% or greater filter efficiency**
- **Manual filter mechanism**
- **provide 125 cfm**
- **a HEPA filter is available**

When used in conjunction with the corresponding Hilti tools and dust removal systems meeting the listed Table 1 requirements, you will have a compliant system as specified in the regulation.

Please contact your local Hilti representative with any additional questions. For additional clarification, please refer to 29 CFR Part 1926 §1153.

Sincerely,

Hilti product team

Hilti, Inc.
7250 Dallas Parkway, Ste 1100
Plano, TX 75024

1-800-879-8000
www.hilti.com



June 23, 2017

Statement on features of Hilti VC 20, 40, 150, and 300 series vacuums:

Regarding OSHA 29 CFR Part 1926 §1153, please note that the Hilti VC 20-U, VC 40-U, VC 40-UE, VC 150-6 X, VC 150-6 XE, VC 150-10 X, VC 150-10 XE, and VC 300-17 X vacuums all meet the following requirements given in Table 1:

- **99% or greater filter efficiency**
- **self-cleaning filter mechanism**
- **provide the below cubic feet per minute (cfm) of suction**
 - **VC 20-U and 40-U: 129 cfm**
 - **VC 150 series: 150 cfm**
 - **VC 300 series: 300 cfm**
- **a HEPA filter is available**

When used in conjunction with the corresponding Hilti tools and dust removal systems meeting the listed Table 1 requirements, you will have a compliant system as specified in the regulation.

Please contact your local Hilti representative with any additional questions. For additional clarification, please refer to 29 CFR Part 1926 §1153.

Sincerely,

Hilti product team

Hilti, Inc.
7250 Dallas Parkway, Ste 1100
Plano, TX 75024

1-800-879-8000
www.hilti.com



ENV SERVICES, INC.
 4758 RESEARCH DRIVE
 SAN ANTONIO, TX 78240
 800-690-3368 / 210-690-3646 FAX

SERVICE WORK ORDER

WORK ORDER NO: 312-146996

CUST PO#:CREDIT CARD

Bill To: TX3592

HILTI INC.
 P.O. BOX 21148
 ATT: ACCOUNTS PAYABLE
 TULSA, OK 74121
 FRANK HIERONYMUS
 918-671-2349

Service Location: TX3592-002

HILTI INC.
 3701 ROYAL LANE
 SUITE 100
 IRVING, TX 75063 972-403-5887
 FRANK HIERONYMUS
 FRANK.HIERONYMUS@HILTI.COM

SERVICE SCHEDULE DATE: _____

SCHEDULE ADMIN: 204 **TECH:** 611

CUSTOMER NOTES / INSTRUCTIONS:

WO OPEN DATE 06-Jun-17

WORKGROUP: _____

SERVICE REQUESTED:TEST AND CERTIFICATION

BILLING TYPE: _____

DETAIL OF SERVICES

Item #	Asset #	Description of Services	Location
1		ONSITE CERTIFICATION TESTING OF 7 NEW VACUUMS FOR COMPLIANCE WITH HEPA ** PLEASE NOTE THAT THE DAY RATE APPLIES TO THE TESTING LISTED IN THE LINE ITEMS BELOW**	
2		ONSITE CERTIFICATION TEST AND CERTIFICATION - NEW VACUUM ITEM NUMBER: 2167143 DESCIPTION: VC 300-17X FLOW RATE: 300 CU FT/MIN	
3		ONSITE CERTIFICATION TEST AND CERTIFICATION - NEW VACUUM ITEM NUMBER: 2167144 DESCIPTION: VC 150-6XE FLOW RATE: 150 CU FT/MIN	
4		ONSITE CERTIFICATION TEST AND CERTIFICATION - NEW VACUUM ITEM NUMBER: 2167145 DESCIPTION: VC 150-10XE FLOW RATE: 150 CU FT/MIN	
5		ONSITE CERTIFICATION TEST AND CERTIFICATION - NEW VACUUM ITEM NUMBER: 2167146 DESCIPTION: VC 150-6XE FLOW RATE: 150 CU FT/MIN	
6		ONSITE CERTIFICATION	

CUSTOMER SIGNATURE : _____

TECH SIGNATURE: 

DATE : _____

DATE : 16 Jun 2017



ENV SERVICES, INC.
 4758 RESEARCH DRIVE
 SAN ANTONIO, TX 78240
 800-690-3368 / 210-690-3646 FAX

SERVICE WORK ORDER

WORK ORDER NO: 312-146996

CUST PO#:CREDIT CARD

Bill To: TX3592

HILTI INC.
 P.O. BOX 21148
 ATT: ACCOUNTS PAYABLE
 TULSA, OK 74121
 FRANK HIERONYMUS
 918-671-2349

Service Location: TX3592-002

HILTI INC.
 3701 ROYAL LANE
 SUITE 100
 IRVING, TX 75063 972-403-5887
 FRANK HIERONYMUS
 FRANK.HIERONYMUS@HILTI.COM

DETAIL OF SERVICES

Item #	Asset #	Description of Services	Location
		TEST AND CERTIFICATION - NEW VACUUM ITEM NUMBER: 2167147 DESCRIPTION: VC 150-10XE FLOW RATE: 150 CU FT/MIN	
7		ONSITE CERTIFICATION TEST AND CERTIFICATION - NEW VACUUM ITEM NUMBER: 2167148 DESCRIPTION: VC 125-6 FLOW RATE: 125 CU FT/MIN	
8		ONSITE CERTIFICATION TEST AND CERTIFICATION - NEW VACUUM ITEM NUMBER: 2167149 DESCRIPTION: VC 125-9 FLOW RATE: 125 CU FT/MIN	

CUSTOMER SIGNATURE : _____

TECH SIGNATURE:  _____

DATE : _____

DATE : 16 Jan 2017



dba ENV Services Testing and Certification, Inc.
 2880 Bergey Road, Suite K
 Hatfield, PA 19440
 (800) 345-6094

Test Report Number
 TX3592-002
Inventory Number
 WO#312-146996

SERVICE REPORT

Customer: HILTI INC. Address: 3701 ROYAL LANE SUITE 100 IRVING, TEXAS 75063 Contact: FRANK HIERONYMUS Telephone: 972/403-5887	ENV Services Technician: JERRY MAXWELL Test Date: 16-Jun-17 Test Frequency: ONE TIME ONLY Equipment Manufacturer: CUSTOM Model Number: VARIOUS SEE WO. Serial Number: SEE WO. Type: VACUUM UNITS Location: WAREHOUSE
--	---

Testing and Certification: The purpose of field testing this equipment is to assess whether it is functioning as designed in compliance with manufacturer's specifications, NIH specifications, NSF Standard #49, or other specifications which may apply. We perform all test procedures in accordance with these standards and as detailed in ENV Services Protocols, applicable copies of which are available on request. Our testing and certification apply only to the equipment and do not signify approval of the use of any hazardous agents or operational procedures.

SERVICE SUMMARY			
	PASS	FAIL	N/A
OVERALL CERTIFICATION	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>

COMMENTS AND RECOMMENDATIONS hepa leak test completed on item numbers 2167143, 2167144, 2167145, 2167146, 2167147, 2167148, and 2167149. All passed.
--

Customer Signature _____
FRANK HIERONYMUS
PLEASE PRINT NAME

Serviced by: Jerry Maxwell
 Date: 16-Jun-17

HEPA VACUUM TEST REPORT

Prepared for:

HILTI Inc.
7250 North Dallas Parkway
Plano, TX 75024

Models: VC20U, VC40U, VC40U /outlet

Attention:

Frank Hieronymus
918-712-2349

Date(s) Tested:

7/13/15

Field Service Technician(s):

Ken Waterhouse



4758 Research Drive
San Antonio, TX 78240
(210) 690-3368
Fax (210) 690-3646

HEPA LEAK TESTING OF HILTI HEPA VACUUM UNITS BENCH TESTING FOR AEROSOL PENETRATION

Setup

Each Vacuum is setup with an internal prefilter bag placed in the base of the bucket and a HEPA filter placed below the motor

Airflow enters the intake and is then passed through the prefilter bag and then is siphoned up through the HEPA filter and then discharged

through louvers on the right and left side of the vacuum housing

Procedure:

Following guidelines within Reference Standard; IES-RP-CC-0034.1

HEPA and ULPA Filter Leak Tests.

A large bag was placed over the outlet side of the Vacuum unit

The Intake airflow was measured with a Velocity meter set for CFM Calculation (135 CFM)

A calculated concentration was followed using an aerosol challenge for >10 micrograms per liter of PAO Aerosol

The Aerosol Photometer was set at a sensitivity of 50 micrograms, and the test proceeded by insertion of aerosol in the intake and sampling the outflow of the air filling the collection bag.

No leakage greater than .005% was detected



Test Setup showing Aerosol Generator on right HILTI VC20U Vacuum in middle with catch bag attached, and Aerosol Photometer on the left

Ken Watrous
 Technical Manager 13 JUL 15

Conclusions:

All Models passed the aerosol penetration leak test of no leakage greater than .005% penetration detected.

See Certificates

Test Equipment Used:

Tec Services Inc. Aerosol Photometer
Model # PH.-5
Serial # 2027
Calibration Date: 29JUN2015

ATI Model 6B Aerosol Generator
6 Nozzle
S# 26536

Velocity Meter
TSI
Model # 9535
S# T95351514002



Certificate No.: ENV/0615-497-5501
 Procedure No.: WI0299000

Control No.: 01263
 Page 1 of 2

UNIT UNDER TEST

Manufacturer: TSI
Model No.: 9535
Serial No.: T95351514002
Cust. Ref. No.: 01263
Description: AIR VELOCITY METER
Date Rec'd: 6/3/2015
Condition Rec'd: GOOD

SUBMITTED BY

Customer: ENV SERVICES, INC (REGION I)
 2880 BERGEY RD
 HATFIELD, PA 19440

P.O. #: ENV/610

Precal: OUT OF SPEC **Final:** IN SPEC



CALIBRATION CERTIFICATE

All calibrations are performed by qualified personnel using instrumentation, procedures and methods which guarantee specifications claimed are reliable. When specified, all calibrations are performed in accordance with current ISO/IEC 17025, ANSI/NCSL Z-540-1, MIL-STD-45662A, and ENV/Pro-Lab Quality Manual - Rev 5. Standards used are traceable to The National Institute of Standards and Technology (NIST). Expanded uncertainties are calculated using methods described in the Guide to the Expression of Uncertainty of Measurement (GUM) utilizing a coverage factor of K=2 (95% confidence) and kept on file at Pro-Lab. At a minimum, standards are selected with an uncertainty of 25% or better, where possible. This certificate and/or data shall not be reproduced except in full, without the written permission of Pro-Lab Management.

Standards Used

Asset #	Description	Certificate Number	Date Due
1064	DUAL CAPACITANCE MANOMETER	ENV/0515-480-5015	5/31/2016
1208	PRESSURE TRANSDUCER	ENV/0515-480-5013	5/31/2016
00985	REFERENCE THERMOMETER	ENV/0314-481-5572A	6/30/2015
986	RTD PROBE	ENV/0314-481-2316	6/30/2015

Temperature: 23.0 C
 Humidity: 54.6 % RH
 Approved By: Michael Blahut

Date Tested: 11-Jun-2015
 Date Due: 30-Jun-2016
 Calibrated By: David Andreas
 Calibration Technician
 E-Signed 11-Jun-2015 8:37 AM

E-Signed 11-Jun-2015 11:05 AM

-- A DIVISION OF ENV SERVICES, INC. --
 2880 BERGEY ROAD SUITE K - HATFIELD, PA 19440-1742 - (800) 992-9108 - FAX (215) 822-6522



Certificate No.: ENV/0615-497-5501
 Procedure No.: WI0299000

Control No.: 01263
 Page 2 of 2

UNIT UNDER TEST

Manufacturer: TSI
Model No.: 9535
Serial No.: T95351514002
Cust. Ref. No.: 01263
Description: AIR VELOCITY METER
Date Rec'd: 6/3/2015
Condition Rec'd: GOOD

SUBMITTED BY

Customer: ENV SERVICES, INC (REGION I)
 2880 BERGEY RD
 HATFIELD, PA 19440

P.O. #: ENV/610

Precal: OUT OF SPEC **Final:** IN SPEC



CALIBRATION DATA

Note: Calibration results may drift from documented values prior to calibration due date attributable to various factors. Results obtained apply to the UUT only and are reflective of conditions at the time of this test.

Velocity

Description	Standard	As Found	Final	Min.	Max.
FPM	30	31	31	27	33
FPM	70	73	73	67	73
FPM	100	103	103	97	103
FPM	150	154	154	145	155
FPM	325	335	335	315	335
FPM	650	652	652	630	670
FPM	1000	1001	1001	970	1030
FPM	1500	1484	1484	1455	1545
FPM	2500	2452	2452	2425	2575
FPM	4500	4543	4543	4425	4575
FPM	5900	5904	5904	5723	6077

TEMPERATURE

Description	Standard	As Found	Final	Min.	Max.
Deg F	73.5	74.6	73.5	73.0	74.0 A



Certificate No.: ENV/0615-478-14854
 Procedure No.: MFR

Control No.: 01289
 Page 1 of 2

UNIT UNDER TEST

Manufacturer: TEC SERVICES
 Model No.: PH-5
 Serial No.: 2027
 Cust. Ref. No.: 01289
 Description: PHOTOMETER
 Date Rec'd: 6/19/2015
 Condition Rec'd: GOOD

SUBMITTED BY

Customer: ENV SERVICES, INC (REGION I)
 2880 BERGEY RD
 HATFIELD, PA 19440
 P.O. #: ENV/600
 Precal: IN SPEC Final: IN SPEC



Calibration Laboratory
 CERT#1591.01

CALIBRATION CERTIFICATE

All calibrations are performed by qualified personnel using instrumentation, procedures and methods which guarantee specifications claimed are reliable. When specified, all calibrations are performed in accordance with current ISO/IEC 17025, ANSI/NCSL Z-540-1, MIL-STD-45662A, and ENV/Pro-Lab Quality Manual - Rev 5. Standards used are traceable to The National Institute of Standards and Technology (NIST). Expanded uncertainties are calculated using methods described in the Guide to the Expression of Uncertainty of Measurement (GUM) utilizing a coverage factor of K=2 (95% confidence) and kept on file at Pro-Lab. At a minimum, standards are selected with an uncertainty of 25% or better, where possible. This certificate and/or data shall not be reproduced except in full, without the written permission of Pro-Lab Management.

Standards Used

Asset #	Description	Certificate Number	Date Due
0152	MULTIMETER	52-VEN-2477095	4/30/2016
00173	MASS FLO METER	ENV/0914-497-191	6/30/2015

Temperature: 22.0 C
 Humidity: 35.0% RH
 Approved By: Michael Blahut

Date Tested: 29-Jun-2015
 Date Due: 30-Jun-2016
 Calibrated By: William Leas, Jr.
 Calibration Technician
 E-Signed 29-Jun-2015 2:08 PM

E-Signed 30-Jun-2015 1:12 PM



Certificate No.: ENV/0615-478-14854
 Procedure No.: MFR

Control No.: 01289
 Page 2 of 2

UNIT UNDER TEST

Manufacturer: TEC SERVICES
 Model No.: PH-5
 Serial No.: 2027
 Cust. Ref. No.: 01289
 Description: PHOTOMETER
 Date Rec'd: 6/19/2015
 Condition Rec'd: GOOD

SUBMITTED BY

Customer: ENV SERVICES, INC (REGION I)
 2880 BERGEY RD
 HATFIELD, PA 19440
 P.O. #: ENV/600
 Precal: IN SPEC Final: IN SPEC



CALIBRATION DATA

Specifications obtained from: TEC SERVICES MODEL PH-5 PHOTOMETER USER MANUAL.

Note: Calibration results may drift from documented values prior to calibration due date attributable to various factors. Results obtained apply to the UUT only and are reflective of conditions at the time of this test.

DC VOLTAGES

Description	Standard	As Found	Final	Min.	Max.
V (V1)	5.15	5.14	5.14	5.10	5.20
V (V2)	12.00	12.00	12.00	11.00	13.00
V (V3)	-12.00	-12.00	-12.00	-12.50	-11.50
V (V4)	24.00	24.00	24.00	23.50	24.50

SAMPLE FLOW

Description	Standard	As Found	Final	Min.	Max.
CFM	1.00	1.00	1.00	0.90	1.10

FUNCTIONAL TEST

Description	Standard	As Found	Final	Min.	Max.
SCANNING PROBE		PASS	PASS		
UPSTREAM RESPONSE + CLEAR TO ZERO		PASS	PASS		
DOWN STREAM RESPONSE + CLEAR TO ZERO		PASS	PASS		



Certificate of Compliance

HILTI VC20U HEPA Vacuum Unit

Hilti, Inc.
7250 North Dallas Parkway
Plano, TX 75024

On this Date: 7/13/2015

Testing conducted in accordance with IES RP-CC-002 & Following guidelines within
Reference Standard; IES-RP-CC-0034.1

Administered By : *Ken Waterhouse*

Conducted by: ENV Services, Inc.
4758 Research Dr.
San Antonio, TX 78240



Certificate of Compliance

HILTI VC40U HEPA Vacuum Unit

Hilti, Inc.
7250 North Dallas Parkway
Plano, TX 75024

On this Date: 7/13/2015

Testing conducted in accordance with IES RP-CC-002 & Following guidelines within Reference Standard; IES-RP-CC-0034.1

Administered By : *Ken Waterhouse*

Conducted by: ENV Services, Inc.
4758 Research Dr.
San Antonio, TX 78240



Certificate of Compliance

HILTI VC40U/Outlet HEPA Vacuum Unit

Hilti, Inc.
7250 North Dallas Parkway
Plano, TX 75024

On this Date: 7/13/2015

Testing conducted in accordance with IES RP-CC-002 & Following guidelines within
Reference Standard; IES-RP-CC-0034.1

Administered By : *Ken Waterhouse*

Conducted by: ENV Services, Inc.
4758 Research Dr.
San Antonio, TX 78240



Certificate of Compliance

HILTI VC 75-1 A22 HEPA Filter Unit

Filter # 2192228

Hilti, Inc.

7250 North Dallas Parkway

Plano, TX 75024

On this Date: April 9, 2018

Testing conducted in accordance with IES RP-CC-002 & Following guidelines within Reference Standard; IES-RP-CC-0034.4

Conducted by: ENV Services, Inc.
4758 Research Dr.
San Antonio, TX 78240

Administered By : *Jerry Maxwell*



Certificate of Compliance

HILTI VC 125-6 HEPA Vacuum Unit

Filter # 203879

Hilti, Inc.

7250 North Dallas Parkway

Plano, TX 75024

On this Date: April 9, 2018

Testing conducted in accordance with IES RP-CC-002 & Following guidelines within Reference Standard; IES-RP-CC-0034.4

Conducted by: ENV Services, Inc.
4758 Research Dr.
San Antonio, TX 78240

Administered By : *Jerry Maxwell*



Certificate of Compliance

HILTI VC 125-9 HEPA Vacuum Unit

Filter # 203879

Hilti, Inc.

7250 North Dallas Parkway

Plano, TX 75024

On this Date: April 9, 2018

Testing conducted in accordance with IES RP-CC-002 & Following guidelines within Reference Standard; IES-RP-CC-0034.4

Conducted by: ENV Services, Inc.
4758 Research Dr.
San Antonio, TX 78240

Administered By : *Jerry Maxwell*



Certificate of Compliance

HILTI VC 150-6X HEPA Vacuum Unit

Filter # 203879

Hilti, Inc.

7250 North Dallas Parkway

Plano, TX 75024

On this Date: April 9, 2018

Testing conducted in accordance with IES RP-CC-002 & Following guidelines within Reference Standard; IES-RP-CC-0034.4

Conducted by: ENV Services, Inc.
4758 Research Dr.
San Antonio, TX 78240

Administered By : *Jerry Maxwell*



Certificate of Compliance

HILTI VC 150-6XE HEPA Vacuum Unit

Filter # 203879

Hilti, Inc.

7250 North Dallas Parkway

Plano, TX 75024

On this Date: April 9, 2018

Testing conducted in accordance with IES RP-CC-002 & Following guidelines within Reference Standard; IES-RP-CC-0034.4

Conducted by: ENV Services, Inc.
4758 Research Dr.
San Antonio, TX 78240

Administered By : *Jerry Maxwell*



Certificate of Compliance

HILTI VC 150-10X HEPA Vacuum Unit

Filter # 203879

Hilti, Inc.

7250 North Dallas Parkway

Plano, TX 75024

On this Date: April 9, 2018

Testing conducted in accordance with IES RP-CC-002 & Following guidelines within Reference Standard; IES-RP-CC-0034.4

Conducted by: ENV Services, Inc.
4758 Research Dr.
San Antonio, TX 78240

Administered By : *Jerry Maxwell*



Certificate of Compliance

HILTI VC 150-10XE HEPA Vacuum Unit

Filter # 203879

Hilti, Inc.

7250 North Dallas Parkway

Plano, TX 75024

On this Date: April 9, 2018

Testing conducted in accordance with IES RP-CC-002 & Following guidelines within Reference Standard; IES-RP-CC-0034.4

Conducted by: ENV Services, Inc.
4758 Research Dr.
San Antonio, TX 78240

Administered By : *Jerry Maxwell*



Certificate of Compliance

HILTI VC 300-17X HEPA Vacuum Unit

Filter # 2177708

Hilti, Inc.

7250 North Dallas Parkway

Plano, TX 75024

On this Date: April 9, 2018

Testing conducted in accordance with IES RP-CC-002 & Following guidelines within Reference Standard; IES-RP-CC-0034.4

Conducted by: ENV Services, Inc.
4758 Research Dr.
San Antonio, TX 78240

Administered By : *Jerry Maxwell*

VACUUM CLEANER

VC 75 / 125 / 150 / 300 OSHA

Hilti developed a vacuum cleaner system with a filter cleaning mechanism and a >99% filter efficiency, compliant with many of the OSHA 1926.1153, Table 1 specified controls.

Set-up

1. Put a filter into the filter compartment. Decide which filter depending on your applications. See filter section for further information.
2. Put filter bag into the tank. Decide which filter bag depending on your applications. See filter bag section for further information.
3. Put hose into head and attach it to the adaptor of the tool. See tool manual for further information on correct adaptor.
4. Plug vacuum cleaner in socket.
5. Start vacuum cleaner by turning control switch on. Verify proper operation of vacuum cleaner.
 - head on correct and sealed
 - no kinks/breaks/plugs in hose
 - check for normal suction at hose end
 - nothing blocking exhaust port
 - For VC 20/40/150/300, verify the automatic filter cleaning mechanism is turned on, and operating (audible thumping every ~15 seconds).
6. Start running the tool only when vacuum cleaner is on.
7. Turn vacuum cleaner off after tool is turned off.

Cleaning and maintenance

1. For VC 75 and VC 125, push manual filter cleaning button every 3 to 5 minutes depending on application, and whenever there is a noticeable change in suction or dust collection..
2. Filter and filter bag needs to be cleaned and exchanged regularly. See filter and filter bag section for further information.

UNIVERSAL FILTER-BAGS / PLASTIC BAGS

Plastic Bag



Universal Bag



Applications

- For dry and wet applications
- Will not increase lifetime of filter, no pre-filtering

- For dry applications
- Virtually dustless recycling / emptying
- Pre-filter, will increase lifetime of filter

How to put bag in vacuum

1. Remove head from tank
2. Put bag into the tank
3. Check that holes are within the vacuum cleaner when installed and that the plastic bag doesn't overlap clamp area
4. Put head back on tank and close clamps properly

1. Remove head from tank
2. Put bag into the tank
3. Connect flange of filter bag to the adapter
4. Put head back on tank and close clamps

Disposal guidelines

- Recycle bag when it is full
- Tie off or seal paper/fleece bags. Twist plastic bags. Roll bucket to nearest sealed receptacle and transfer bag to garbage.
- To be recycled normally (dispose of bag according to local regulations)

- Close cap when bag is full or needs to be recycled
- Dispose of bag according to local regulations.

DO'S AND DON'TS WITH UNIVERSAL FILTER-BAGS / PLASTIC BAGS

Plastic Bag



Universal Bag



Do's

- Dispose of bag when it is full

- Use filter bags for all dry applications
 - Increases lifetime of your tool
 - Increase lifetime of your filter
- Dispose of bag when it is full
- Mandatory for all wood applications
- Connect flange of filter bag properly into adapter

Don'ts

- Fill plastic bag to completely full, it can rip apart
- Overlap the clamp area with the plastic bag

- Shake full filter-bag
 - Dust can exit
 - Bag can rip apart
- Use bag for wet applications

DO'S AND DON'TS WITH FILTERS

Do's

- Maximize life of filter by utilizing the vacuums filter cleaning mechanism (action is optimized by sealing hose for 3-5 filter cleaning cycles) with automatic filter cleaning (close hose for a 3-5 cycles)
- Power cleaning: Remove hose, close inlet for 3-5 automatic filter cleaning cycles
- Use performance filters (PTFE) in order to have a longer lifetime of your tool, longer lifetime of the filter and less blockage of the filter
- Filter sealing needs to be properly installed
- During filter change, clean up filter frame and sealing area
- Check filter condition before starting an application

Don'ts

- Mix dry and wet applications. Dry filters used for wet applications needs to be exchanged with a wet/dry filter and dried before using it for dry applications
- Manually cleaning the filter can damage the filter and lead to decreased vacuum life and poor dust control capability damaged -> a damaged or missing filter can lead to a broken turbine since dust can enter (reduces lifetime of vacuum cleaner)
 - Banging against the wall
 - Cleaning with high-pressured air
 - Use water jet / air pressure jet to clean the filter
 - Use sharp things e.g. wrench etc. to clean the filter
- Use vacuum cleaner without a filter

FILTER CLEANING AND EXCHANGE

Filter needs to be cleaned when:

- Notably less suction power
 - Clean filter with automatic filter cleaning
- Dust is coming out of the vacuum cleaner. Indication that the filter is damaged or blocked.
- Visual check shows that filter needs to be cleaned

Filter needs to be exchanged when:

- Dust is coming out of the vacuum cleaner. Indication that filter is damaged or blocked.
- Even after cleaning the filter, suction power is insufficient
- Visual check shows that filter needs to be exchanged due to a high volume of dust near or inside the filter



Hilti, Inc. (U.S.) 1-800-879-8000
en español 1-800-879-5000
www.hilti.com

Hilti (Canada) Corporation 1-800-363-4458
www.hilti.com